



Streamline Stainless Steel Wallplates

Features and Benefits

The Streamline series has traditionally been a family of low-profile plastic and steel wallplates designed for applications requiring minimum labeling and port designation. The plastic wallplates have a label for easy identification of the wallplate.

All Streamline Wallplates are available in one, two, three, four and six port wallplate configurations. The plastic series also provides a 4 Port 1U configuration. Streamline Wallplates utilize DataGate Plus Jacks and 1U/Single-position fiber and copper modules. Streamline Wallplates are UL-approved and are rear-loading to resist tampering.

- Stainless Steel wallplates utilize DataGate Plus Jacks and single-position fiber and copper modules
- Perfect for schools and other institutional applications
- Low profile for inconspicuous network connecting
- Rear loading to reduce tampering


Approvals: UL 1863

Material: Stainless Steel and Thermoplastic UL94V-0

Reference Information


Parts List

- Wallplate
- (2) Mounting Screws




1 Port Wallplate

Dimensions: 115.06mm x 70.10mm x 10.41mm
4.53"H x 2.76"W x .41"D
Shipping Weight: 64g (2.3 oz.)




3 Port Wallplate

Dimensions: 115.06mm x 70.10mm x 10.41mm
4.53"H x 2.76"W x .41"D
Shipping Weight: 64g (2.3 oz.)




2 Port Wallplate

Dimensions: 115.06mm x 70.10mm x 10.41mm
4.53"H x 2.76"W x .41"D
Shipping Weight: 64g (2.3 oz.)



4 Port Wallplate

Dimensions: 115.06mm x 70.10mm x 10.41mm
4.53"H x 2.76"W x .41"D
Shipping Weight: 64g (2.3 oz.)



6 Port Wallplate

Dimensions: 115.06mm x 70.10mm x 10.41mm
4.53"H x 2.76"W x .41"D
Shipping Weight: 64g (2.3 oz.)

ORDERING INFORMATION

Order No.	Description
WSS-00001	1 Port Stainless Steel Streamline Wallplate
WSS-00002	2 Port Stainless Steel Streamline Wallplate
WSS-00003	3 Port Stainless Steel Streamline Wallplate
WSS-00004	4 Port Stainless Steel Streamline Wallplate
WSS-00006	6 Port Stainless Steel Streamline Wallplate

MOLEX PREMISE NETWORKS

Molex Premise Networks
Corporate Headquarters
New Hampshire, USA
Tel: 1 603 324 0200
www.molexpn.com

European Headquarters
Hampshire, England
Tel: 44 (0) 1489 527111
www.molexpn.co.uk

Pac Rim Headquarters
Victoria, Australia
Tel: 61 3 9971 7111
www.molexpn.com.au