











Product Information

Erem Medical Applications

The examples below show models that have been developed for particular applications in various medical fields. Several of them can serve in one field whereas one tool can also be used for different jobs. Detailed features will kindly be given on request. Please submit your requirements with explanations and possibly samples, parts, for free tests.




Cutters, Pliers

	Order No.	Description	dental / ortho	cardio-vascular*	various fields
	503ETST 110 mm	High precision tip cutter for fine stainless wires like MP35N, catheters, stents, guide wires		X	
	576TX 115 mm	High precision side cutter for stainless wires, catheters, coiled wires		X	
	576TX-1 115 mm	Same as above but rounded tips		X	
	599TFO 115 mm	For fine stainless steel coil wires, Kevlar® or Vectran® braided wires		X	
	147A 120 mm	For larger wires, compound action	X	X	X
	622NC (not illustrated) 110 mm	For fine soft wires		X	X
	632NCF 110 mm	Absolute full flush cut on soft materials like Silicon tubings		X	X
	541 130 mm	Reverse action, for temporary enlarging, then inserting synthetic tubings on human liquid analysis, fixed or portable machines		X	X
	9000 Series 115 mm	Example No. 9139. A complete line of orthodontic, hard Chrome plated pliers and cutters	X		
	552E, 552S 120 mm	Precision strippers for very fine wires up to 60 µ, In electronics devices, echographs, X-rays, etc.			X

*Production of catheters, stents, pace makers, etc.


Product Information

Tweezers



Order No.	Description	dental / ortho	cardio-vascular*	various fields
2ASA-RU 120 mm	For non sticking handling of adhesive labels and ribbons			X
5FSA, 5MBS, 115 mm	Super fine tips tweezers, working under microscopes, biology			X
15AGS 115 mm	Cutting tiny wires like those used in hearing aids production			X
29Y 135 mm	Smallest stripper, allows work in very confined areas like μ -sensors. AWG 30>40			X
45 (not illustrated) 120 mm	Holding, reverse action tweezers for endodontic obturators (root canals in molar teeth)	X		
258SA 120 mm	Synthetic tips for handling delicate parts without touching with metal			X
940AS 120 mm	Ligature tie placer with locking device	X		

Various



Order No.	Description	dental / ortho	cardio-vascular*	various fields
3000 Series	Vacuum micro-manipulators, for picking up small parts like lenses, biological culture preparations, tiny components for micro electronic boards used in hearing aids production, etc.			X

*Production of catheters, stents, pace makers, etc.

For more information please contact:

Cooper Tools GmbH
Carl-Benz-Str. 2
74354 Besigheim, Germany
Tel.: +49-7143-5800
Fax: +49-7143-580108

Erem S.A.
Rue de la Roselière 8
1400 Yverdon les Bains, Switzerland
Tel.: +41-24-4261206
Fax: +41-24-4250977