

RoHS Compliant



PX-279/ PX-275

PCIe 8xRS232 1MBaud

"SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



Description

PCI Express Card providing eight RS232 serial ports connected using 9 pin cables. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOs, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Drivers for Windows 32 bit and 64 bit Operating Systems including Windows 2000, XP, Server 2003, Vista, Server 2008 and Windows 7.

PCI Express is the latest standard in PC connectivity.

With Brainboxes' industry renowned Lifetime Warranty and Lifetime Support!

Features

- 8 port RS232
- PCI Express x1, x4, x8 & x16 lane slots socket size
- 32 Byte Tx and 32 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit & 64 bit Editions
- Windows Server 2008 32 bit & 64 bit Editions ^{64-bit}
- Windows Vista 32 bit & 64 bit editions
- Windows Server 2003 32 bit & 64 bit Editions


As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.

Options



PX-279:
PCIe 8xRS232 1MBaud

PX-275:
PCIe 8xRS232 DB25
1MBaud




ORDER

Description

PCIe 8xRS232 1MBaud
PCIe 8xRS232 DB25 1MBaud

Code

PX-279
PX-275



PCIe 8xRS232 1MBaud

PX-279/ PX-275: Full Specification

<p>Port</p> <table border="1"> <tr><td>Pin 1</td><td>DCD</td></tr> <tr><td>Pin 2</td><td>RXD</td></tr> <tr><td>Pin 3</td><td>TXD</td></tr> <tr><td>Pin 4</td><td>DTR</td></tr> <tr><td>Pin 5</td><td>GND</td></tr> <tr><td>Pin 6</td><td>DSR</td></tr> <tr><td>Pin 7</td><td>RTS</td></tr> <tr><td>Pin 8</td><td>CTS</td></tr> <tr><td>Pin 9</td><td>RI</td></tr> </table> <p>RS232 Pinout (9 Pin Male)</p>	Pin 1	DCD	Pin 2	RXD	Pin 3	TXD	Pin 4	DTR	Pin 5	GND	Pin 6	DSR	Pin 7	RTS	Pin 8	CTS	Pin 9	RI	<p>Ports</p> <p>Connector</p> <p>FIFO size</p> <p>Operating Distance</p> <p>Cable</p>	<p>8 x RS232</p> <p>DB9 Connector - 9 Pin Male (PX-279) DB25 Connector - 25 Pin Male (PX-275)</p> <p>32 RX FIFO + 32 TX FIFO</p> <p>EIA - RS232 Standard</p> <p>8 port cable (78 way D to 8x9 Pin Male) (PX-279) 8 port cable (78 way D to 8x25 Pin Male) (PX-275)</p>
Pin 1	DCD																			
Pin 2	RXD																			
Pin 3	TXD																			
Pin 4	DTR																			
Pin 5	GND																			
Pin 6	DSR																			
Pin 7	RTS																			
Pin 8	CTS																			
Pin 9	RI																			
<p>Port Settings</p> <p>921,600 baud</p>	<p>Baud Rate</p> <p>Data Bits</p> <p>Parity</p> <p>Stop Bits</p> <p>Flow Control</p> <p>Tx/Rx Modes</p>	<p>921,600</p> <p>5,6,7 or 8</p> <p>Odd, Even, None, Mark or Space</p> <p>1, 1.5 or 2</p> <p>RTS/CTS, DSR/DTR, XON/XOFF</p> <p>Point to Point</p>																		
<p>Interface</p>	<p>OS Compatibility</p> <p>BUS</p>	<p>Microsoft Windows 8 32 bit & 64 bit Editions Microsoft Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit Editions Windows Vista 32 bit & 64 bit Editions Windows Server 2003 32 bit & 64 bit Editions</p> <p>PCI Express x1, x4, x8 & x16 lane slots</p>																		
<p>Approvals</p>	<p>Other Approvals</p> <p>Microsoft Approvals</p>	<p>AEO (C-TPAT) Microsoft Certified Gold Partner WEEE RoHS METL EMC: CE TAA</p> <p>Windows 7 32 bit & 64 bit Editions Windows Server 2008 32 bit & 64 bit editions Windows Vista 32 bit & 64 bit editions Windows Server 2003 32 bit & 64 bit editions Windows XP 32 bit & 64 bit editions</p>																		
<p>General</p>	<p>PCB Layers</p> <p>Power Consumption</p> <p>Weight</p> <p>Size</p>	<p>4</p> <p>490mA @ 3.3V, 210mA @ 12V</p> <p>0.112 kg, 0.25 pounds (PX-279) awaiting (PX-275)</p> <p>null</p>																		
<p>Box Content</p>	<p>Packaging</p> <p>Card</p>	<p>Installation CD including manual, Microsoft signed drivers & utilities</p> <p>PCIe 8xRS232 1MBaud</p> <p>8 port cable (78 way D to 8x9 Pin Male) (PX-279) 8 port cable (78 way D to 8x25 Pin Male) (PX-275)</p>																		
<p>Product Support</p>	<p>Warranty</p> <p>Support</p>	<p>Lifetime (online registration required)</p> <p>Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team</p>																		
<p>Additional</p>	<p>OEM option</p> <p>Made In</p> <p>Customisable</p>	<p>Available for bulk buy OEM</p> <p>Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"</p> <p>Brainboxes operate a "Perfect Fit Custom Design" policy for volume</p>																		

Other PCI Express Cards: 1 Port RS232 | 2 Port RS232 | 4 Port RS232 | 8 Port RS232 | 1 Port RS422/485 | 2 Port RS422/485 | 4 Port RS422/485
 Other Brainboxes Ranges: PCI | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial