

**Crimping tool
PZ 6/5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Crimping tools for wire end ferrules, with and without plastic collars**

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

Order No.	9011460000
Type	PZ 6/5
Version	Crimping tool, Crimping tool for wire-end ferrules, 0.25 mm ² , 6 mm ² , Trapezoidal indentation crimp
GTIN (EAN)	4008190165352
Qty.	1 pc(s).

**Crimping tool
PZ 6/5**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	200 mm	Weight	423 g
Net weight	388.2 g		

Technical data

Version	Mechanical, without interchangeable inserts
---------	---

Contact description

Type of contact	Wire-end ferrules with/without plastic collars	Crimping range, min.	0.25 mm ²
Crimping range, max.	6 mm ²		

Tool data - crimping

Crimping profile 1, min.	0.25 mm ²	Crimping type/profile	Trapezoidal indentation crimp
Wire end ferrules cross-section, min.	0.25 mm ²	Crimping profile 1, max.	0.5 mm ²
Wire end ferrules cross-section, max.	6 mm ²	Crimping profile 2, min.	0.75 mm ²
Crimping profile 2, max.	1.5 mm ²	Crimping profile 3, min.	2.5 mm ²

Classifications

ETIM 2.0	EC000168	ETIM 3.0	EC000168
UNSPSC	23-17-16-04	eClass 4.1	21-04-03-01
eClass 5.1	21-04-03-01	eClass 6.0	21-04-38-90
eClass 7.0	21-04-38-90		

Product information

Descriptive text ordering data	Additional accessories can be found in Chapter J
Descriptive text accessories	Information and ordering data for wire end ferrules - see chapter J accessories wire end ferrules
Description of article	Crimping tool for wire end ferrules with/without plastic collar, 0,25 bis 6 mm ²
Product description	<ul style="list-style-type: none"> • Crimp complies with Euro-Norm EN 60947-1 • Approval according to VG 95211 (military designation VG 95 236 T 14 B 002) • Five crimping stations corresponding to the conductor cross-sections • Wire-end ferrule insertion from the side

Approvals

Approvals



Data sheet...

**Crimping tool
PZ 6/5**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

