

## ULTRASONIC CLEANING MADE SIMPLE

FOR BOTH HOME & PROFESSIONAL USE

*Ultrasonic cleaning is a unique phenomenon. Millions of tiny bubbles are created when ultrasonic sound is passed through liquid. It is these tiny bubbles combined with a huge pressure that creates incredible cleaning results.*

# ULTRA 8020-H

WITH DEGAS AND HEATER

## PRODUCT FEATURES

- Large stainless steel tank
- Digital programmable timer
- Built-in 80 watt heater
- Enhanced circuit protection
- Sealed electronics

## EXAMPLE APPLICATIONS

<b>HOME</b>	JEWELLERY
<b>OFFICE</b>	WATERPROOF WATCHES
<b>JEWELLERS</b>	RAZOR HEADS
<b>DENTAL INDUSTRY</b>	PRINTER HEADS
<b>HOME ENTHUSIAST</b>	TOOTHBRUSH HEADS
<b>CAR &amp; BIKE MECHANICS</b>	DENTAL TOOLS
	MACHINE ITEMS
	+ many more uses

- Ultrasonic operating frequency 35,000Hz
- Mains power for quality cleaning results
- Supplied ready to use - no assembly required
- Full CE and RoHS approval



The Ultra-8020 Ultrasonic Cleaner has been designed for the professional user. With our continued research & development we found the ideal size, features, specification and of course price to cater for many different applications.

Whether in your jewellery shop, dental studio or workshop, the Ultra-8020 will handle your cleaning requirements with ease.

Featuring a large 1.6litre stainless steel tank with programmable timer, so that you can clean without having to interrupt your work.

The Ultra-8020 also has a built-in heater which when programmed will heat the water to a useful 65 degrees, enhancing your cleaning ability. To finish the package a basket to hold your smaller items is included.



## SPECIFICATION

Model Name :	ULTRA 8020-H
Timer Settings :	Digital timer From 5 - 30 mins automatic shut-off
Tank Size :	1 . 6L stainless steel Tank to max line
Ultrasonic Frequency :	35,000Hz (42 kHz)
Power Consumption :	160W Max
Power Supply :	AC 220-240V 50Hz
Unit Dimensions (LxWxH) :	265x 230x 1 8 0 mm
Internal Tank Dimensions (LxWxH) :	183 x 153 x 55mm MAX
Weight (NET) :	2200g
Mains Fuse :	3A

## ACCESSORIES

### INCLUDED

Plastic basket for smaller items



All orders must be in multiples of box quantity shown : eg: 12 x Ultra 8020-H

Prices and information is correct at time of printing. James Products Ltd reserves the right to vary prices & specifications, including colours with or without notice and at such times in such manner as they see fit.