

## USB to VGA Multi Monitor External Video Adapter

StarTech ID: USB2VGAE2




The USB2VGAE2 USB to VGA external video adapter is the perfect multi-monitor VGA solution for office applications and Internet browsing.

The USB video adapter features a small form factor and enables a USB 2.0 port to be used with a VGA port. A cost-saving multi-monitor or dual display option that can be used as an external graphics card for either laptop or desktop applications.

The USB video adapter can be used with up to four additional (five total) USB2VGAE2 USB video adapters, creating multiple VGA connections that can be used to further extend or mirror the desktop shown on the existing display - all without having to open the computer case to add extra video cards.

### Application Diagram



Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### **Applications**

- Add a secondary display adapter and extend your desktop display without taking apart your computer to install a new video card
- Add multiple (up to five) monitors / projectors to your computer setup using one USB2VGAE2 device for each additional display
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs enabling connection to a secondary display
- Connect multiple monitors to a single computer to create engaging multimedia presentations
- Use the adapter to connect your PC to your television for showing family pictures and movies
- Increase productivity by running multiple applications on different screens, check your email on one display and work on a document in the other
- Great for researchers and writers offering the ability to have reference material on one display and a working document copy on the other

### **Features**

- Optimal performance at 1440x900 (higher resolutions supported) and ideal for use with 17" to 19" monitors or smaller
- Works with desktop and laptop computers
- No power adapter required
- Includes easy to use software that allows for, multi-display management and EDID monitor detection for increased compatibility with displays
- Simple installation

Technical Specifications

Warranty	2 Years
Memory	16MB SDRAM
Chipset ID	MCT - Trigger 1+
Connector Type(s)	1 - USB A (4 pin) Male
Connector Type(s)	1 - VGA (15 pin; High Density D-Sub) Female
Supported Resolutions	Standard(16/32 bit): 1600x1200, 1400x1050, 1280x1024, 1280x960, 1152x864, 1024x768, 800x600  Widescreen(16/32 bit): 1680x1050, 1400x900, 1280x800, 1280x768, 1152x864, 1024x768, 800x600
OS Compatibility	Windows 8 (32/64) Windows 7(32/64) Windows Vista (32/64) Windows XP (32/64) Drivers are WHQL certified
Color	Gray
Cable Length	457.2 mm [18 in]
Product Length	75 mm [3 in]
Product Width	42 mm [1.7 in]
Product Height	50 mm [2 in]
Product Weight	80 g [2.8 oz]
System and Cable Requirements	One available USB 2.0 port
Shipping (Package) Weight	640 g [22.6 oz]
Included in Package	1 - USB to VGA Adapter
Included in Package	1 - Driver and Software CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

