

**Passeinsatz für Einsätze E14 4 A  
COMBI CHECK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE-Norm 0682, section 401
- high peak voltage strength
- the right tester for every application

**General ordering data**

Order No.	<a href="#">9918860000</a>
Type	COMBI CHECK
Version	2-pole voltage tester, Yes
GTIN (EAN)	4032248405749
Qty.	1 pc(s).

## Passeinsatz für Einsätze E14 4 A COMBI CHECK

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Dimensions

Weight	290 g	Net weight	290 g
--------	-------	------------	-------

### Technical data

Version	Protective bag
---------	----------------

### Product data

Rated voltage, min.	6 V	AC voltage measuring range	6-690 V
Frequency range, min.	0 Hz	Frequency range, max.	100 Hz
Rated voltage, max.	690 V AC/DC	Protection degree	IP65
Battery type	1.5 V type AAA battery	Tested and approved according to	EN/IEC 61243-3 :2010-10 (VDE 0682 part 401)
Peak voltage resistance	8 kV	Display	LED
DC voltage display	6,12, 24, 50, 120, 230, 400, 690 V	AC voltage display	6,12, 24, 50, 120, 230, 400, 690 V

### Classifications

ETIM 2.0	EC000494	ETIM 3.0	EC000494
UNSPSC	41-11-36-37	eClass 4.1	27-20-03-08
eClass 5.1	27-20-03-08	eClass 6.0	27-20-03-08
eClass 7.0	27-20-03-08		

### Product information

Description of article	Voltage tester up to 690 V/ 100 Hz LED
Product description	<ul style="list-style-type: none"> <li>• Phase sequence indicator</li> <li>• Single-pole phase test</li> <li>• Batteries included</li> </ul>

### Approvals

Approvals

**Passeinsatz für Einsätze E14 4 A  
COMBI CHECK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

