

# BVS-02

# Bottle Vertical Level Sensor

## BVS Series

- Fits 1L bottle
- Low level sensing
- Goes closed circuit as liquid level drops
- Reed Switch Reliability (UL File E153493)
- Interface Option Available



### The BVS-02

From our range of vertical liquid level sensors which offer design engineers reed switch reliability. The design allows for sensing low liquid levels from a standard Ink or beverage concentrate bottle. Provided with a liquid draw off tube to maximise liquid extraction. The design allows for rapid removal and installation of a full bottle.

### FEATURES


- PTFE suction pipe for liquid draw off
- Overall length less than 220mm installed
- 38mm Screw Cap
- External Fit
- Polypropylene Material

### APPLICATIONS

- Additive low level
- Ink low level
- Water Low Level
- Concentrate Low Level

### dimensions

#### BVS-02



## performance specifications

### Material, Design and Operation

Mounting	Vertical
Housing Material	Polypropylene
Housing Colour	Black
Float Material	Foamed Polypropylene
Float Colour	White
Contact Form	A
Contact Material	Ruthenium
Maximum Switching Volts (VAC)	200
Maximum Switching Volts (VDC)	200
Maximum Switching Current (Amp)	0.75
Maximum Power (Watt)	30
Connection Type	Stripped Cables
Cable Type	22AWG, PVC insulated
Cable Length	2 x 0.5M single insulated
Cable Colour	White outer Blue/Brown inner
Minimum Specific Gravity	0.65
Operate Temperature Range	-30°C to +85°C
Medium/Liquid	Water/Ink
Sealing Component	EPDM Cap Seal
Mounting Shock	50g for 11mS duration
Operate Mode	N/C with float at bottom stop
IP Rating	IP65

The information in this sheet has been carefully reviewed and is believed to be accurate; however, no responsibility is assumed for inaccuracies. Furthermore, this information does not convey to the purchaser of such devices any license under the patent rights to the manufacturer. Measurement Specialties, Inc. reserves the right to make changes without further notice to any product herein. Measurement Specialties, Inc. makes no warranty, representation or guarantee regarding the suitability of its product for any particular purpose, nor does Measurement Specialties, Inc. assume any liability arising out of the application or use of any product or circuit and specifically disclaims any and all liability, including without limitation consequential or incidental damages. Typical parameters can and do vary in different applications. All operating parameters must be validated for each customer application by customer's technical experts. Measurement Specialties, Inc. does not convey any license under its patent rights nor the rights of others.

## ordering info

The BVS-02 is from our BVS Series of Bottle Vertical Level Sensors.

The Series is available in alternative with a number of standard options including:

- 33mm cap size
- Shorter length for 0.5L bottle

**Please see the BVS Series part number tree.**