

# Hex Extensions

## Male Hex Drive with 1/4" Male Square



Part Number	Hex Drive In.	Type of Lock	Overall Length In.	Overall Length mm
EX-250	1/4	Pin	1 3/8	35
EX-250-B•	1/4	Ball	1 3/8	35
EX-250-2•	1/4	Pin	2	51
EX-250-B-2•	1/4	Ball	2	51
EX-250-3•	1/4	Pin	3	76
EX-250-B-3•	1/4	Ball	3	76
EX-250-4•	1/4	Pin	4	102
EX-250-B-4•	1/4	Ball	4	102
EX-250-5•	1/4	Pin	5	127
EX-250-B-5•	1/4	Ball	5	127
EX-250-6•	1/4	Pin	6	152
EX-250-B-6•	1/4	Ball	6	152
EX-250-8•	1/4	Pin	8	203
EX-250-B-8•	1/4	Ball	8	203
EX-250-12•	1/4	Pin	12	305
EX-250-B-12•	1/4	Ball	12	305
EX-262	5/16	Pin	1 1/2	38
EX-262-4	5/16	Pin	4	102
EX-262-B-4	5/16	Ball	4	102
EX-262-6	5/16	Pin	6	152
EX-251	7/16	Pin	1 3/8	35
EX-251-B	7/16	Ball	1 3/8	35
EX-251-2•	7/16	Pin	2	51
EX-251-B-2	7/16	Ball	2	51
EX-251-3	7/16	Pin	3	76
EX-251-6	7/16	Pin	6	152
EX-251-8	7/16	Pin	8	203
EX-251-10	7/16	Pin	10	254

## Male Hex Drive with 3/8" Male Square



Part Number	Hex Drive In.	Type of Lock	Overall Length In.	Overall Length mm
EX-250•	1/4	Pin	1 3/8	35
EX-370•	1/4	Pin	1 5/8	41
EX-370-B•	1/4	Ball	1 5/8	41
EX-370-2•	1/4	Pin	2	51
EX-370-B-2•	1/4	Ball	2	51
EX-370-3•	1/4	Pin	3	76
EX-370-B-3•	1/4	Ball	3	76
EX-370-4•	1/4	Pin	4	102
EX-370-B-4•	1/4	Ball	4	102
EX-370-5•	1/4	Pin	5	127
EX-370-6•	1/4	Pin	6	152
EX-370-B-6•	1/4	Ball	6	152
EX-370-8•	1/4	Pin	8	203
EX-370-B-8	1/4	Ball	8	203
EX-370-10•	1/4	Pin	10	254
EX-370-B-10	1/4	Ball	10	254
EX-380•	5/16	Pin	1 1/2	38
EX-380-B•	5/16	Ball	1 1/2	38
EX-380-2•	5/16	Pin	2	51
EX-380-B-2	5/16	Ball	2	51
EX-380-3•	5/16	Pin	3	76
EX-380-4	5/16	Pin	4	102
EX-380-6	5/16	Pin	6	152
EX-371•	7/16	Pin	1 3/4	45
EX-371-2•	7/16	Pin	2	51
EX-371-2 3/4•	7/16	Pin	2 3/4	70
EX-371-3•	7/16	Pin	3	76
EX-371-B-3•	7/16	Ball	3	76
EX-371-4•	7/16	Pin	4	102
EX-371-5•	7/16	Pin	5	127
EX-371-6•	7/16	Pin	6	152
EX-371-8•	7/16	Pin	8	203
EX-371-10•	7/16	Pin	10	254
EX-371-12•	7/16	Pin	12	305
EX-371-15•	7/16	Pin	15	381

• Indicates a commonly requested item that is either in stock or has a max typical leadtime of 4 weeks from the factory. No minimum on these items.

# Hex Extensions

## Male Hex Drive with 1/2" Male Square



Part Number	Hex Drive In.	Type of Lock	Overall Length In.	Overall Length mm
EX-500-2*	1/4	Pin	2	51
EX-500-B-2*	1/4	Ball	2	51
EX-500-3*	1/4	Pin	3	76
EX-500-B-3*	1/4	Ball	3	76
EX-500-4*	1/4	Pin	4	102
EX-500-B-4*	1/4	Ball	4	102
EX-500-6*	1/4	Pin	6	152
EX-500-B-6	1/4	Ball	6	152
EX-512-2	5/16	Pin	2	51
EX-512-B-2	5/16	Ball	2	51
EX-512-3	5/16	Pin	3	76
EX-512-B-4	5/16	Ball	4	102
EX-501-2*	7/16	Pin	2 1/8	54
EX-501-B-2*	7/16	Ball	2 1/8	54
EX-501-3*	7/16	Pin	3	76
EX-501-B-3*	7/16	Ball	3	76
EX-501-4*	7/16	Pin	4	102
EX-501-B-4	7/16	Ball	4	102
EX-501-5*	7/16	Pin	5	127
EX-501-B-5	7/16	Ball	5	127
EX-501-6*	7/16	Pin	6	152
EX-501-B-6	7/16	Ball	6	152
EX-501-8*	7/16	Pin	8	203
EX-501-B-8	7/16	Ball	8	203
EX-501-10*	7/16	Pin	10	254
EX-501-B-10	7/16	Ball	10	254
EX-501-12	7/16	Pin	12	305
EX-501-B-12*	7/16	Ball	12	305
EX-501-15	7/16	Pin	15	381
EX-502	5/8	Pin	2	51
EX-502-B	5/8	Ball	2	51
EX-502-3*	5/8	Pin	3	76
EX-502-B-3	5/8	Ball	3	76
EX-502-B-4	5/8	Ball	4	102
EX-502-5	5/8	Pin	5	127
EX-502-6	5/8	Pin	6	152
EX-502-8	5/8	Pin	8	203

## Male Hex Drive with 5/8" Male Square



Part Number	Hex Drive In.	Type of Lock	Overall Length In.	Overall Length mm
EX-620-3	7/16	Pin	3	76
EX-620-6	7/16	Pin	6	152
EX-621-3	5/8	Pin	3	76
EX-621-B-3	5/8	Ball	3	76
EX-621-6	5/8	Pin	6	152
EX-621-8	5/8	Pin	8	203

## Male Hex Drive with 3/4" Male Square



Part Number	Hex Drive In.	Type of Lock	Overall Length In.	Overall Length mm
EX-757-3	7/16	7/32 Drill Hole	3	76
EX-757-B-3	7/16	Ball	3	76
EX-758-4*	5/8	7/32 Drill Hole	4	102
EX-758-B-4	5/8	Ball	4	102
EX-758-6	5/8	7/32 Drill Hole	6	152
EX-758-9	5/8	7/32 Drill Hole	9	229

# Extensions

## Threaded Screw Shank



Part Number	Male Square In.	Male Thread In.	Overall Length In.	Overall Length mm	Body Diameter In.	Body Diameter mm
TH-256	1/4	1/4-28	1 5/8	41	7/16	11
TH-376	3/8	1/4-28	1 5/8	41	1/2	13
TH-250	1/4	1/4-24	1 5/8	41	7/16	11
TH-370	3/8	1/4-24	1 3/4	45	1/2	13
TH-372	3/8	1/4-20	1 3/4	45	1/2	13

\* Indicates a commonly requested item that is either in stock or has a max typical leadtime of 4 weeks from the factory. No minimum on these items.