

Uncontrolled document as of February 20, 2013. Refer to website for up to date specifications.

LIGHTS
2400
StealthLite



Submersible 

StealthLite™ 2400 Flashlight

Popular with firefighters and adventure seekers. The unique easy slide thumb switch on the StealthLite 2400 Flashlight is easy to operate, even with gloves. The tough resin body is corrosion proof and resistant to extreme temperatures. The Xenon lamp is powered by 4 AA alkaline cells (included) for a bright beam that penetrates thick smoke, fog, and dust. Attach the StealthLite to one of our optional helmet light holder clips and you have a hands-free light for work or play. This light is submersible.

Body Material: LEXAN EXL Resin

Minimum Pack 6 ea.

Packaged Weight: 8.1 oz.






Assorted Packs available - 2 black, 2 yellow, 2 orange.

StealthLite™ 2400 Flashlight Specifications

StealthLite™ 2400 Flashlight Configurations

Cat. #	Description
--------	-------------

High	
LIGHT SOURCE	Xenon
BATTERIES	4 AA Alkaline (Included)
CHARGE TIME	N/A
VOLTAGE	6
LENGTH	6.49" (16.5 cm)
WEIGHT w/ BATTERIES	7.1 oz. (0.2 kg)
WEIGHT w/o BATTERIES	3.5 oz. (0.1 kg)

FL1 STANDARD	High	
LIGHT OUTPUT 	45 LUMENS	
RUNTIME (hours:min) 	3h 45m	
BEAM DISTANCE (meters) 	125m	
PEAK BEAM INTENSITY (candela) 	3934cd	
WATERPROOF & SUBMERSIBLE 	IPX7	IPX7

2400 StealthLite™ 2400 Flashlight (Carded)

2400PL StealthLite™ 2400 Flashlight w/ Photoluminescent Shroud

NSN List


NSN #	Description
6240-01-468-8407	2404 Lamp Module
6230-01-462-9320	2400 Black
6230-01-496-3639	2400 Zone 1 (Peli)
6230-01-428-7464	2400C Yellow
6230-01-462-9320	2400CNVG Black
6230-01-525-9820	2400C Lime Green (2400-010-135)
6230-01-397-6341	2400C

StealthLite™ 2400 Flashlight Accessories

Cat. #	Description
700	Helmet Light Holder
710	Helmet Light Holder
711	Helmet Light Holder
712	Helmet Light Holder
750	Helmet Light Holder
760	Helmet Light Holder
770	Universal Helmet Light Holder
2404	StealthLite™ 2400 Xenon Lamp Module
2407	Cordura® Holster
2403PL	Photoluminescent Shroud

StealthLite™ 2400 Flashlight Approvals

 Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.

 Class I, Div. 2; Gp. ABCD, T3A.

 US Class I, Div. 1, GP.D, CL.I, Zone 1, GP. IIA OPERATING TEMP. CLASS T3 CONFORMS TO STD. UL 783 Energizer E91 only
Intertek 3091325

Pelican Products, Inc.

23215 Early Avenue • Torrance, CA 90505 • Phone: (310) 326-4700 • (800) 473-5422 • Fax: (310) 326-3311
e-mail: CSR.Consumer@pelican.com • www.pelican.com