

Permatex, Inc.
10 Columbus Blvd.
Hartford, CT 06106 USA
Telephone: 1-87-Permatex
(877) 376-2839
Emergency: 800-255-3924 (ChemTel)
International Emergency: +01-813-248-0585

Material Safety Data Sheet

1. PRODUCT IDENTIFICATION

Product Name: LARGE DIAMETER THREADLOCKER RED 50ML
Item No: 27750
Product Type: Anaerobic

2. COMPOSITION/INFORMATION ON INGREDIENTS

Component	Weight%	ACGIH; TLV-TWA	OSHA PEL
METHACRYLATE MONOMER 25852-47-5	40-70	Not listed	Not listed
POLYESTER RESIN MIXTURE	30-50	Not listed	Not listed
DIMETHYLBENZYL HYDROPEROXIDE 80-15-9	<3	Not listed	Not listed

3. HAZARDS IDENTIFICATION

Toxicity: May cause eye and skin irritation. At elevated temperatures may cause irritation of the respiratory tract. Ingestion may irritate digestive tract and cause nausea, vomiting and diarrhea. High concentrations may cause central nervous system (CNS) depression. May cause skin sensitization.

Primary Routes of Entry: Eye and skin contact, ingestion, inhalation

Signs and Symptoms of Exposure: Repeated skin contact may cause allergic skin reactions. Ingestion may cause nausea and vomiting. Inhalation overexposure may cause irritation, coughing and flu-like symptoms. May cause pain, redness or swelling of the eyes and excessive blinking and tear production.

Medical Conditions Recognized as Being Aggravated by Exposure: Preexisting skin disorders.

4. FIRST AID MEASURES

Ingestion: If swallowed, DO NOT induce vomiting. Keep individual calm. Obtain medical attention.

Inhalation: Move to fresh air in case of accidental inhalation of vapours. Obtain medical attention.

Skin Contact: Wash off with soap and water. If skin irritation persists, call a physician.

Eye Contact: In case of contact, immediately flush eyes with plenty of water for at least 15 minutes and get medical attention if irritation persists.

5. FIRE FIGHTING MEASURES

Flash Point °F(C°): >200°F TCC

Recommended Extinguishing Media: Dry chemical, Carbon dioxide, Foam

Special Fire-Fighting Procedures: Firefighters should wear self-contained breathing apparatus.

Hazardous Products of Combustion: Oxides of carbon

Unusual Fire/Explosion Hazards: None.

Lower Explosive Limit: Not determined

Upper Explosive Limit: Not determined

6. ACCIDENTAL RELEASE MEASURES

Spill Procedures: Maintain good ventilation. Take up with an inert absorbent. Store in a closed waste container until disposal.

7. HANDLING AND STORAGE

Storage: Store below 100°F.

Handling: Avoid prolonged skin contact. Keep away from eyes. Wash thoroughly after handling.

Product Name: LARGE DIAMETER THREADLOCKER
RED 50ML

Item No: 27750

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Eyes: Safety glasses.
Skin: Neoprene or nitrile gloves recommended.
Ventilation: General; local exhaust ventilation as necessary to control any air contaminants to within their exposure limits (or to the lowest feasible levels when limits have not been established) during the use of this product.
Respiratory Protection: In case of insufficient ventilation, wear suitable respiratory equipment.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Red liquid
Odor: Mild
Boiling Point: >200°F
pH: Does not apply
Solubility in Water: Insoluble
Specific Gravity: 1.07-1.17
VOC(Wt.%): <3%
Vapor Pressure: Not determined
Vapor Density (Air=1): >1
Evaporation Rate: Not determined

10. STABILITY AND REACTIVITY

Chemical Stability: Stable at normal conditions
Hazardous Polymerization: Will not occur
Incompatibilities: Strong oxidizers
Conditions to Avoid: Heat.
Hazardous Products of Combustion: Oxides of carbon

11. TOXICOLOGICAL INFORMATION

See Section 3

12. ECOLOGICAL INFORMATION

No data available

13. DISPOSAL CONSIDERATIONS

Recommended Method of Disposal: Disposal should be made in accordance with federal, state and local regulations..
US EPA Waste Number: NH - Not a RCRA Hazardous Waste Material

14. TRANSPORTATION INFORMATION

DOT (49CFR 172)

Ground Transport (DOT)

DOT Shipping Name: Not regulated
Hazard Class: None
UN/ID Number: None

IATA

Proper Shipping Name: Not regulated
Class or Division: None
UN/ID Number: None

IMDG

Proper Shipping: Not regulated
Hazard Class: None
UN Number: None

Marine Pollutant: None

15. REGULATORY INFORMATION

SARA 313 Chemicals: The following component(s) is listed as a SARA Section 313 Toxic Chemical.

DIMETHYLBENZYL HYDROPEROXIDE

Product Name: LARGE DIAMETER THREADLOCKER
RED 50ML

Item No: 27750

California Proposition 65: No California Prop 65 chemicals are known to be present at or above the No Significant Risk Level

TSCA Inventory Status: All components of this product are listed (or exempt) on the EPA TSCA inventory.

16. OTHER INFORMATION

Estimated NFPA Rating: HEALTH 2, FLAMMABILITY 1, REACTIVITY 1.

Estimated HMIS Classification: HEALTH 2, FLAMMABILITY 1, PHYSICAL HAZARD 0

NFPA is a registered trademark of the National Fire Protection Assn.

HMIS is a registered trademark of the National Paint and Coatings Assn.

Prepared By: Denise Boyd, Manager-Environmental, Health & Safety
Company: Permatex, Inc. 10 Columbus Blvd. Hartford, CT USA 06106

Revision Date: January 13, 2011

Revision 2

Number:

Telephone No.: 1-87-Permatex (877) 376-2839