

Lockout Tool Box – S1017 – S1020 – S1023

Master Lock® offers kits specific for maintenance operations.

- ✓ Resistant & lightweight toolbox
- ✓ Rugged, strong, large storage capacity
- ✓ Polypropylene cover & base
- ✓ Lockable Riveted Steel Latch
- ✓ Riveted Handle
- ✓ Steel Hinge pin in Lid
- ✓ 3 Dimensions: S1017: W 420 x L 230 x D 216 mm
S1020: W 495 x L 230 x D 230 mm
S1023: W 571x L 254 x D 254 mm
- ✓ Available filled and unfilled
- ✓ Contents match maintenance needs
 - ✓ Electrical Lockout – S1117ES31KA
 - ✓ Valve Lockout – S1117VS31KA
 - ✓ Electrical & Valve Lockout – S1117VES31KA



S1117ES31KA



S1117VS31KA



S1117VES31KA

Kits Contents

S1117ES31KA 17" Toolbox with Electrical Lockout Assortment & 3 x S31KARED Padlock

Product Model	Description	Qty
S1017	Empty Toolbox 42 x 23 x 21,6 cm	1
S31KARED	Zenex Padlock - 38 mm shackle length - Keyed Alike - Key retaining	3
S806	Adjustable Cable Lockout - Length 1,80m - 4 mm cable diameter	1
420	Safety Hasp, 2,71 cm diameter Jaws, Red Handle	2
491B	New Grip Tight Lockout Device for standard size breaker toggles	1
S2390	Miniature Circuit Breaker for standard toggle	3
S2393	Universal Miniature Circuit Breaker	2

S1117VS31KA 17" Toolbox with Valve Lockout Assortment 3x S31KARED Padlock

Product Model	Description	Qty
S1017	Empty Toolbox 42 x 23 x 21,6 cm	1
S31KARED	Zenex Padlock - 38 mm shackle length - Keyed Alike - Key retaining	3
420	Safety Hasp, 2,71 cm diameter Jaws, Red Handle	2
S806	Adjustable Cable Lockout - Length 1,80m - 4 mm cable diameter	3
480	Gate Valve Cover fits 2,71 to 8,12 cm diameter Handles	1
481	Gate Valve Cover fits 5,41 to 13,54 cm diameter Handles	1
482	Gate Valve Cover fits 10,83 to 17,60 cm diameter Handles	1
S3068MLP	Bloque vanne quart de tour / vanne papillon - Universel	1

S1117VES31KA 17" Toolbox with Valve and Electrical Lockout Assortment 6x S31KARED Padlock

Product Model	Description	Qty
S1017	Empty Toolbox 42 x 23 x 21,6 cm	1
S31KARED	Zenex Padlock - 38 mm shackle length - Keyed Alike - Key retaining	6
420	Safety Hasp, 2,71 cm diameter Jaws, Red Handle	2
S806	Adjustable Cable Lockout - Length 1,80m - 4 mm cable diameter	3
480	Gate Valve Cover fits 2,71 to 8,12 cm diameter Handles	1
481	Gate Valve Cover fits 5,41 to 13,54 cm diameter Handles	1
482	Gate Valve Cover fits 10,83 to 17,60 cm diameter Handles	1
S3068MLP	Universal Handle-On Ball Valve Lockout	1
S2390	Miniature Circuit Breaker for standard toggle	6
S2393	Universal Miniature Circuit Breaker	2