

User Manual

Table of Contents

1.0 Introduction.....	1
2.0 Specifications.....	1
3.0 Package Contents.....	2
4.0 Panel Descriptions.....	2
5.0 Connection and Operation.....	3

MHL Bridge to VGA and Stereo Audio Adapter

DEAR CUSTOMER

Thank you for purchasing this product. For optimum performance and safety, please read these instructions carefully before connecting, operating or adjusting this product. Please keep this manual for future reference.

1.0 INTRODUCTION

The MHL Bridge to VGA and Stereo Audio Adapter is an accessory made with one purpose to convert your MHL Host, like MHL Phone or Tablet, to your VGA display or projector and audio amplifier. That's to say, this adapter can convert MHL AV signal to VGA video and stereo audio signal.

Features

This MHL cable has many features that enable it to perform in a superior manner. Among those features you will find:

- Uses a single, thin adapter to connect the MHL mobile device to the VGA display.
- Connects Micro-USB female port to computer or Power Adapter for charging and getting power.
- Built-in MHL Receiver converts MHL signal to analog VGA video and stereo audio.
- Supports all bandwidth between 25-75MHz.

2.0 SPECIFICATIONS

Signal Inputs/Output	
Input Connector	Micro-USB Male x1
Output Connector	VGA Female x1
Other Port	
Micro-USB Female	Micro-USB Female x1 for charging
Headset Jack	Earphone Jack Female x1 for 2ch audio
Mechanical	
Size(L-W-H)	63*41*22 mm
Weight (Net)	60g
Warranty	
Limited Warranty	1 Year Parts and Labor
Environmental	
Operating Temperature	0 °C to +70°C
Operating Humidity	10% to 85 % RH (no condensation)
Storage Temperature	-10°C to +80°C

Storage Humidity	5% to 90 % RH (no condensation)
Power Requirement	
External Power Supply	No
Regulatory Approvals	
Converter Unit	FCC,CE,UL
Power Supply	No
Accessories Adapter	
User Manual	English version


Note: Specifications are subject to change without notice.

3.0 PACKAGE CONTENTS

Before attempting to use this unit, please check the packaging and make sure the following items are contained in the shipping carton:

- Main unit
- User's Manual

4.0 PANEL DESCRIPTIONS



1. Micro USB male
Connect the port to Phone or Tablet with Micro USB port and support MHL Standard.
2. Micro USB Female

Connect the Port to computer or Power Adapter for charging and getting power.

3. VGA Female

Connect the Port to VGA display screen or projector.

4. Headset Jack

Connect the Port to 3.5mm headset or audio amplifier.

5.0 CONECTION DIAGRAM

