



The worldwide leader in thermal management solutions.

[News](#) [About Us](#) [Contact Us](#) [Global Manufacturing](#) [Shop Aavid](#)

[Products](#)

[Solutions](#)

[Industries](#)

[Submit Query](#)

[Your Account](#)

[Logout](#)  
[Cart](#)

[Knowledge Center](#)

[Design Help](#)

# 530002B02500G

TO-220, TO-220-single gauge (0.020")



QTY IN STOCK: 2,335

ENTER QTY:

[VIEW PRICE](#)

Extruded heat sink with large radial fins and solderable pins

This non-electronic component is functionally unaffected by the normal soldering or reflow processes used for semiconductor circuits. The heat resistance time or heat resistance temperature is not applicable for the component.

**Cross Reference:** 6300B-2

**Height:** 63.50

**Mount Orientation:** Vertical

**Finish:** Black Anodize


**RoHS:** compliant

[Download PCN](#)


**Thermal Resistance:** 2.60

**Additional Drawing Dimensions:**

A Dim: 63.5 | B Dim: 18.29 | C Dim: 3.17



X Dim: 12.70 (0.500) | Y Dim: 0.79 (0.031) | Z Dim: 2.67 (0.105)




**Need assistance?**  
Call us: 1-855-32-AAVID  
Email: [estore@aavid.com](mailto:estore@aavid.com)  
[» Help Page](#)

**Check Distributor Stock**  
Enter a part number for pricing and availability.  
 [go!](#)

**Learn More**  
[»Request a Sample](#)  
[»Request a Quote](#)  
[»Ask an Engineer](#)

**The Fine Print**  
[Product Return Policy](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)



Pins

### Customer Assistance

- Contact Us
- Get Design Assistance
- Find a Distributor
- Find a Sales Rep
- Request a Quote
- Placing an Order
- Terms and Conditions
- Returns

### Popular Products

- Fans
- Extrusions
- Board Level
- Liquid Cooling
- Heat Pipe Technology
- Heat Sink Accessories
- Interface Materials

### Our Company

- News and Events
- Management Team
- Worldwide Locations
- Directions to Headquarters
- Disclaimer
- Customer Survey
- Privacy Policy

### Connect with Aavid

Sign up for Aavid News & Alerts

Like / Follow / Connect



© Copyright 2013 Aavid Thermalloy, LLC.

USA: 1.855.32.AAVID Europe: 39.051.764002 Asia: 86.21.6115.2000 x 8122