

Tool accessorie
STRIPAX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



- For flexible and solid conductors with PVC insulation
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No splicing of single conductors
- Adjustable for different insulation thicknesses
- Cable with double insulation in two processing steps without special adjustment
- No play in self-adjusting cutting unit
- Long-lasting
- Optimised ergonomic design

General ordering data

Order No.	9005000000
Type	STRIPAX
Version	Tool accessorie, Stripping and cutting tool, Flexible and solid conductors with PVC insulation, 10 mm ² , 25 mm
GTIN (EAN)	4008190072506
Qty.	1 pc(s).

**Tool accessorie
STRIPAX**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	190 mm	Weight	175 g
Net weight	222 g		

Max. cutting performance

Conductor cross-section (cutting capacity)	6 mm ²
--	-------------------

Max. insulation stripping performance

Cable type	Flexible and solid conductors with PVC insulation	Conductor cross-section, min.	0.08 mm ²
Conductor cross-section, max.	10 mm ²	Conductor cross-section, min. AWG	AWG 28
Conductor cross-section, max. AWG	AWG 7	Stripping length, max.	25 mm

Classifications

ETIM 2.0	EC000163	ETIM 3.0	EC000163
UNSPSC	23-17-16-04	eClass 4.1	21-04-03-01
eClass 5.1	21-04-03-01	eClass 6.0	21-04-38-90
eClass 7.0	21-04-37-06		

Product information

Description of article	Stripping tool for up to 10 mm ²
Product description	<ul style="list-style-type: none"> • Stripping: PVC-insulated flexible wires from 0.08 to 10 mm² (~ AWG 28 to 7) • Cutting: PVC-insulated flexible wires from 0.08 to 10 mm² (~ AWG 28 to 7) • Processing of multi-conductors, with thin flat ribbon cables and even multiple conductors in one operation • No damaging of the conductor due to special, self-adjustable stripping blades

Approvals

Approvals



Data sheet...

**Tool accessorie
STRIPAX**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

