

## WD 5.200 MP

The powerful and versatile WD 5.200MP has a 1600 W motor and boasts an extra large 25 litre stainless steel container. It removes everything from liquid to dust and rubble to leaves. Its power-tool triggered auto-start synchronises both tool and vac for superb dust extraction whilst sanding and sawing. The blower function dislodges dust from crevices, corners and radiators and even inflates airbeds and some paddling pools.

### Standard accessories:

- Suction hose 2.2 m 35 mm
- Suction tubes 2 piece 0.5 m 35 mm Plastic
- Wet and dry floor tool Clips with 2 rubber and 2 brush inserts
- Crevice tool
- Adapter for connecting electric tools
- Cartridge filter Standard
- Blower function
- Plug switch: ON/OFF/AUTO
- Bumper bar
- Parking position
- Power control
- Comfortable 3in1 carry handle
- Rotary switch (On/Off)
- Practical hose and accessory storage
- Tray for keeping tools



**Order no.: 1.347-810.0**

### Technical data

Air flow rate (l/s)	75
Vacuum (mbar/kPa)	220/22
Length of cord access. (m)	5
ID accessory (mm)	35
Max. intake performance (W)	1600
Container capacity / material l	25/Stainless steel
Voltage (V)	220-240
Weight (kg)	8.4
Dimensions (L x W x H) (mm)	450x400x600

## Details

### Description

The powerful and versatile WD 5.200MP has a 1600 W motor and boasts an extra large 25 litre stainless steel container. It removes everything from liquid to dust and rubble to leaves. The blower function dislodges dust from crevices, corners and radiators and even inflates airbeds and some paddling pools. Its liquid pick up can even empty blocked sinks. The power-tool triggered auto-start synchronises both tool and vac for superb dust extraction whilst sanding and sawing. Equipped with a cartridge filter, a wet/dry floor tool and power tool adaptor. All accessories can be stored safely on the machine.

---

## Accessories

### Accessory kits

#### Coarse dirt kit

Extensive vacuuming kit with enlarged nominal diameter (60 mm) for all types of coarse dirt. Suitable for wood chippings, debris, gravel, crushed stones, small stones, leaves, soil or bark mulch.

Order no. 2.637-945.0



#### Car interior cleaning kit

Extensive accessory kit for all jobs in the car. For cleaning car boots, footwells, dashboards, seats, side pockets, footmats, etc.

Order no. 2.862-128.0



#### Household vacuuming set, 4-piece

Extensive accessory kit for all household cleaning tasks. Suitable for floors, corners, upholstery, etc.

Order no. 2.638-510.0



#### Vacuum kit for power tools

Flexible suction hose (1 m) including adapter for connecting hose to the dust exhaust connection of power tools (e.g. jigsaws, grinders, drills, planes, etc.) For clean DIY.

Order no. 2.863-112.0



### Filter

#### Nano-coated cartridge filter

Nano-coated cartridge filter reduces suction power loss, increases dust retention, suitable for wet and dry use without filter replacement.

Order no. 6.414-960.0



#### Paper filter bag

High-performance 2-ply paper filter bag. High-strength filter bags for reliable fine dust retention. Contains: 5 bags

Order no. 6.904-409.0



### Special applications

#### Basic coarse dirt/ash filter

Coarse dirt/ash filter for cleaning fireplaces, tiled stoves, barbecues, sauna ovens, etc., as well as removing coarse dirt.

Order no. 2.863-139.0



## Special applications

### Extension suction tube, 35 mm

Practical extension suction tube for greater flexibility. Suction tube can be extended for difficult to reach areas, e.g. high ceilings.

**Order no. 2.863-148.0**



### 3.5 m extension suction hose

3.5 m extension suction hose for greater flexibility. Practical extension for, e.g. easier cleaning of stairs or cars.

**Order no. 2.638-955.0**



### Metal crevice tool (for coarse dirt/ash filter)

Extra-long metal crevice tool (360 mm) for removing ash or coarse dirt in difficult to reach areas. Applications: fireplaces, saunas, tiled stoves, barbecues, etc.

**Order no. 2.640-951.0**



### Premium coarse dirt/ash filter

Premium coarse dirt/ash filter with fine filter suitable for cleaning fireplaces, tiled stoves, barbecues, sauna ovens, etc., as well as removing coarse dirt.

**Order no. 2.863-161.0**



### Extension suction tube, 60 mm

Practical extension suction tube for greater flexibility. Suction tube can be extended for difficult to reach areas, e.g. high ceilings.

**Order no. 2.863-149.0**



## Vacuating tools

### Nozzle for wet and dry use.

Universal nozzle for wet and dry use on carpets and hard floors. Nozzle with rubber lip suitable for removing liquids.

**Order no. 2.863-204.0**



### Turbo upholstery tool VC 6 und DS 5600

**Order no. 2.903-001.0**



### Brush with soft bristles

Brush with extra soft bristles for gentle cleaning of sensitive surfaces in the car, e.g. dashboards or centre consoles.



## Vacuuming tools

---

**Order no. 2.863-147.0**

---

### **Brush with hard bristles**

Brush for thoroughly cleaning car upholstery and carpets. Hard brush easily removes dried dirt.



**Order no. 2.863-146.0**

---

### **Car vacuuming tool**

Handy car vacuuming tool for quick and easy cleaning – from the footwell to the boot.



**Order no. 2.863-145.0**

---

### **Extra-long crevice tool (350 mm)**

Extra-long crevice tool for difficult to reach areas such as crevices, gaps, cracks and similar, e.g. between upholstery, side pockets in cars or between walls and furniture.



**Order no. 2.863-144.0**

---