

HC-EVO-B06-SHWSC-2SSM32-PLRBK

Order No.: 1407624

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407624>

HEAVYCON EVO box mounting base, plastic, B6, with single locking latch, height:74 mm, with gland, 2 x M32, one of the two openings for the screw connections is sealed but can be broken open using a screwdriver, with protective cover.

Commercial data

EAN	 4 046356 776868
Pack	1
Customs tariff	85389099
Gross weight in pieces	157.60 g
Country of Origin	PL

Product notes

WEEE/RoHS-compliant since:
03/07/2012



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

General data

Note	For contact inserts HC-B6, BB10, DD24, M.
Design	B6
Height	74 mm
Width	57 mm

Length	84 mm
Housing type	Box mounting bases
Color	black
Locking type	With single locking latch
No. of cable exits	2
Cable exit	Lateral
Type of the screw connection	2x M32
Protective cover	Yes
Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Polyamide
Seal material	NBR
Material lock	Polyamide
Material, protective cover	Polyamide
Inflammability class according to UL 94	V0
Connection	One of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

Certificates

Certification

Certifications applied for:


Certification Ex:

Accessories

Item	Designation	Description
General		
1407697	HC-B06-SL-PLBK	Replacement single locking latch for HEAVYCON EVO housing type B6, PA
1407706	HC-B06-SP-RBK	Profile gasket for HEAVYCON EVO supporting base element type B6
1407673	HC-K-KV-M32(12-21)BK	Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 12 - 21 mm, WAF 36, screw connection: M32
1407673	HC-K-KV-M32(12-21)BK	Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 12 - 21 mm, WAF 36, screw connection: M32

Drawings

Dimensioned drawing



Dimensional drawing

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;