

Housing - - 1407634

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




HEAVYCON EVO panel mounting base, plastic, B10, with double locking latch, height: 27 mm, with flat gasket

Product Features

- Lower costs than metal version
- Low weight
- Lower risk of condensation
- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Completely corrosion-resistant
- Halogen-free plastic
- Impact test according to IK 08



Key commercial data

Packing unit	1
GTIN	 4 046356 776967
Custom tariff number	85389099

Technical data

General data

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24. Not for D series terminal adapters.
Design	B10
Height	30.5 mm
Width	53 mm
Length	93.5 mm
Housing type	Panel mounting base

Housing - - 1407634

Technical data

General data

Color	black
Locking type	With double locking latch
Protective cover	No
Degree of protection for housing	IP65 protection when the connector is inserted
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Polyamide
Seal material	NBR
Material lock	Polyamide
Inflammability class according to UL 94	V0
Length of the assembly cutout	65 mm
Width of the assembly cutout	35 mm
Assembly instructions	Not for D series terminal adapters

Classifications

ETIM

ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502
UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209

Accessories

Accessories

Housing - - 1407634

Accessories

Flat gasket - HC-B10-SG-RBK - 1407703



Replacement flat gasket for HEAVYCON EVO supporting base element type B10

Profile seal - HC-B10-SP-RBK - 1407707



Profile gasket for HEAVYCON EVO supporting base element type B10

Double locking latch - HC-B10-24-DL-PLBK - 1407696



Replacement double locking latch for HEAVYCON EVO housing, HC-B10/HC-B16/HC-B24, PA

Protective covers - HC-B10-BC-HI-PLBK - 1407693




HEAVYCON EVO hinged protective cover, type B10 for EVO supporting base element, IP65, PA

Drawings

Housing - - 1407634

Dimensioned drawing



Panel cutout

Housing - - 1407634

Dimensioned drawing

