

HC-EVO-B10-SHFDC-2SSM32-PLRBK

Order No.: 1407639

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407639>

HEAVYCON EVO box mounting base, plastic, B10, for double locking latch, height:74 mm, with gland, 2 x M32, one of the two openings for the screw connections is sealed but can be broken open using a screwdriver, with protective cover.

| Commercial data | |
|------------------------|--------------------------------------------------------------------------------------------------------|
| EAN |  4 046356 777018 |
| Pack | 1 |
| Customs tariff | 85389099 |
| Gross weight in pieces | 156.30 g |
| Country of Origin | PL |

Product notes

WEEE/RoHS-compliant since:
03/07/2012

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

| Technical data | |
|---------------------|--------------------------------------------------|
| General data | |
| Note | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Design | B10 |
| Height | 74 mm |
| Width | 57 mm |

| | |
|-----------------------------------------|---------------------------------------------------------------------------------------------------------|
| Length | 93 mm |
| Housing type | Box mounting bases |
| Color | black |
| Locking type | For double locking latch |
| No. of cable exits | 2 |
| Cable exit | Lateral |
| Type of the screw connection | 2x M32 |
| Protective cover | Yes |
| Degree of protection for housing | IP65 |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Housing material | Polyamide |
| Seal material | NBR |
| Material, protective cover | Polyamide |
| Inflammability class according to UL 94 | V0 |
| Connection | One of the two openings for the screw connections is sealed but can be broken open using a screwdriver. |

Certificates

Certification

Certifications applied for:


Certification Ex:

Accessories

| Item | Designation | Description |
|----------------|----------------------|-----------------------------------------------------------------------------------------------------------------------|
| General | | |
| 1407696 | HC-B10-24-DL-PLBK | Replacement double locking latch for HEAVYCON EVO housing, HC-B10/HC-B16/HC-B24, PA |
| 1407693 | HC-B10-BC-HI-PLBK | HEAVYCON EVO hinged protective cover, type B10 for EVO supporting base element, IP65, PA |
| 1407707 | HC-B10-SP-RBK | Profile gasket for HEAVYCON EVO supporting base element type B10 |
| 1407673 | HC-K-KV-M32(12-21)BK | Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 12 - 21 mm, WAF 36, screw connection: M32 |

Drawings

Dimensioned drawing



Dimensional drawing

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;