











# Wallplates

## Combination Wallplates, 2-Gang

### Combination Wallplates, 2-Gang

Description	Color	Nylon Standard	Nylon Mid-Size	Material	Metal Catalog Number	
 2-Gang, 1-Toggle, 1-Duplex	Almond	<b>NP18AL</b>	<b>NPJ18AL</b>	Aluminum	①	
	Black	<b>NP18BK</b>	<b>NPJ18BK</b>	Brass	①	
	Brown	<b>NP18</b>	<b>NPJ18</b>	Brass Plated	<b>SBP18</b>	
	Gray	<b>NP18GY</b>	<b>NPJ18GY</b>	Chrome	<b>SCH18</b>	
	Ivory	<b>NP18I</b>	<b>NPJ18I</b>	S/S 302/304	<b>SS18</b>	
	Light Almond	<b>NP18LA</b>	<b>NPJ18LA</b>	S/S 430	<b>SS18L</b>	
	Office White	<b>NP18OW</b>	<b>NPJ18OW</b>	Steel, Almond*	<b>SP18AL</b>	
	Red	<b>NP18R</b>	<b>NPJ18R</b>	Steel, Gray*	<b>SP18G</b>	
	White	<b>NP18W</b>	<b>NPJ18W</b>			
	 2-Gang, 1-Duplex, 1-Decorator	Almond	<b>NP826AL</b>	<b>NPJ826AL</b>	Aluminum	①
Black		<b>NP826BK</b>	<b>NPJ826BK</b>	Brass	<b>SB826</b>	
Brown		<b>NP826</b>	<b>NPJ826</b>	Brass Plated	①	
Gray		<b>NP826GY</b>	<b>NPJ826GY</b>	Chrome	①	
Ivory		<b>NP826I</b>	<b>NPJ826I</b>	S/S 302/304	<b>SS826</b>	
Light Almond		<b>NP826LA</b>	<b>NPJ826LA</b>	S/S 430	-	
Office White		<b>NP826OW</b>	<b>NPJ826OW</b>			
White		<b>NP826W</b>	<b>NPJ826W</b>			
 2-Gang, 1-Toggle, 1-Decorator		Almond	<b>NP126AL</b>	<b>NPJ126AL</b>	Aluminum	①
		Black	<b>NP126BK</b>	<b>NPJ126BK</b>	Brass	<b>SB126</b>
	Brown	<b>NP126</b>	<b>NPJ126</b>	Brass Plated	<b>SBP126</b>	
	Gray	<b>NP126GY</b>	<b>NPJ126GY</b>	Chrome	①	
	Ivory	<b>NP126I</b>	<b>NPJ126I</b>	S/S 302/304	<b>SS126</b>	
	Light Almond	<b>NP126LA</b>	<b>NPJ126LA</b>	S/S 430	<b>SS126L</b>	
	White	<b>NP126W</b>	<b>NPJ126W</b>	Steel, Almond*	<b>PJS126AL</b>	
				Steel, Gray*	<b>PJS126G</b>	
 2-Gang, 1-Duplex, 1-Telephone .406 in. (10.3) Hole Strap Mount	Almond	<b>NP128AL</b>	-	Aluminum	-	
	Black	<b>NP128BK</b>	-	Brass	-	
	Brown	<b>NP128</b>	-	Brass Plated	-	
	Gray	<b>NP128GY</b>	-	Chrome	-	
	Ivory	<b>NP128I</b>	-	S/S 302/304	-	
	White	<b>NP128W</b>	-	S/S 430	-	
 2-Gang, 1-Toggle, 1-Telephone .406 in. (10.3) Hole Strap Mount	Almond	<b>NP112AL</b>	-	Aluminum	-	
	Black	<b>NP112BK</b>	-	Brass	-	
	Brown	<b>NP112</b>	-	Brass Plated	-	
	Gray	<b>NP112GY</b>	-	Chrome	-	
	Ivory	<b>NP112I</b>	-	S/S 302/304	-	
	Office White	<b>NP112OW</b>	-	S/S 430	-	
	White	<b>NP112W</b>	-			
 2-Gang, 1-Decorator, 1-Telephone .406 in. (10.3) Hole Strap Mount	Almond	<b>NP1226AL</b>	-	Aluminum	-	
	Black	<b>NP1226BK</b>	-	Brass	-	
	Brown	<b>NP1226</b>	-	Brass Plated	-	
	Gray	<b>NP1226GY</b>	-	Chrome	-	
	Ivory	<b>NP1226I</b>	-	S/S 302/304	-	
	White	<b>NP1226W</b>	-	S/S 430	-	
 2-Gang, 1-Single Receptacle 1.40 in. (35.6) Hole, 1-Duplex	Almond	<b>NP78AL</b>	-	Aluminum	①	
	Brown	<b>NP78</b>	-	Brass	①	
	Gray	<b>NP78GY</b>	-	Brass Plated	①	
	Ivory	<b>NP78I</b>	-	Chrome	①	
	White	<b>NP78W</b>	-	S/S 302/304	<b>SS78</b>	
				S/S 430	-	
 2-Gang, 1-Single Recept. 1.60 in. (40.6) Hole, 1-Duplex	Almond	-	-	Aluminum	①	
	Brown	-	-	Brass	①	
	Ivory	-	-	Brass Plated	①	
	White	-	-	Chrome	①	
				S/S 302/304	<b>SS8720</b>	
				S/S 430	-	

Note: All standard and mid-size nylon wallplates feature pre-inserted captive screws for faster assembly, up to 6-gang.

① Available as a custom wallplate. See pages K-33 to K-38. Consult custom wallplates section for additional openings and combinations.

\* Powder coat paint finish.