


MSTB 2,5/19-ST-5,08-LR

Order No.: 1809050



<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1809050>

Plug component, Nominal current: 12 A, Rated voltage (III/2): 320 V,
Number of positions: 19, Pitch: 5.08 mm, Connection method: Screw
connection, Color: green, Contact surface: Tin

| Commercial data | |
|------------------------|--|
| EAN |  4 046356 702508 |
| Note | Made-to-order |
| Pack | 50 |
| Customs tariff | 85366990 |
| Gross weight in pieces | 33.99 g |
| Country of Origin | DE |

Product notes

WEEE/RoHS-compliant since:
23/09/2011



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Certificates



Certification

cULus Recognized

Certifications applied for:


Certification Ex:

Accessories

| Item | Designation | Description |
|---------------------|--------------------------|--|
| General | | |
| 1733169 | EBP 2- 5 | Insertion bridge, fully insulated, for plug-in connectors with 5.0 or 5.08 mm pitch, no. of positions: 2 |
| Marking | | |
| 1051993 | B-STIFT | Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm |
| 0805108 | SK 5,08/2,8:SO | Marker cards, white, Mounting type: Adhesive, For terminal block width: 5.08 mm |
| 0804293 | SK 5,08/3,8:FORTL.ZAHLEN | Marker cards, Card, white, labeled, Horizontal: Consecutive numbers 1 - 10, 11 - 20, etc. up to 91 - (99)100, Mounting type: Adhesive, For terminal block width: 5.08 mm |
| 0803883 | SK U/2,8 WH:UNBEDRUCKT | Marker cards, Sheet, white, Unlabeled, Can be labeled with: Plotter, Office-Drucksysteme, Mounting type: Adhesive |
| Plug/Adapter | | |
| 1734634 | CP-MSTB | Coding profile, is inserted into the slot on the plug or inverted header, red insulating material |
| Tools | | |
| 1205053 | SZS 0,6X3,5 | Actuation tool, for ST terminal blocks, insulated, also suitable for use as a bladed screwdriver, size: 0.6 x 3.5 x 100 mm, 2-component grip, with non-slip grip |

Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;