


T-2 Pilot Single Socket Assemblies

Choose your cap or lens...

Round Lens Square lens

Add a T-2 Pilot lamp...
6PSB
12PSB
24PSB
48PSB
60PSB
120PSB

And insert into socket.



Dimensions:
Round Lens: 0.70" x 0.48" high
Square Lens: 0.70" x 0.48" high
Sockets: 1.31" M.O.L.
Mounting Hole: 0.50" diameter

Tinnerman Clip:
Single Socket Assemblies are supplied with 0.63" x 0.91" Tinnerman Clips that hold the assemblies firmly to the panel

Socket

Mfr.'s Type	Description	Each
30152	Round Flange Socket For T-2 Pilot Lamp	2.20

Lenses For 30151, 30152 & 30153 Socket Assemblies

Round Type	Square Type	Lens Color	Each
...	30170/SQ/LR	Red	.69
...	30172/SQ/LA	Amber	.69
...	30173/SQ/LW	White	.69
...	30174/SQ/LG	Green	.69

Universal Lamp Housings - For T-2 Slide Base Pilot Lamps

Flat Top Translucent Jeweled Dome Transparent Dome Fluted



Add a T-2 Pilot lamp

Neoprene Washers

Dimensions
Lenses: Diameter 0.63"; Height: 0.38"
Socket: Front of panel to end of terminals: 0.91"
Mounting Hole: .719" diameter



File No. E31557(M)

File No. LR20904

Mfr.'s Type 30099 Socket \$3.46

Universal Lamp Housings - For T-2½ & T-3¼ Miniature Bayonet Base Lamps

Flat Top Translucent Jeweled Dome Transparent Dome Fluted



T-2½ Lamp

T-3¼ Lamp

Neoprene Washers

Dimensions
Lenses: Diameter 0.63"; Height: 0.38"
Socket: Front of panel to end of terminals: 1.68"
Mounting Hole: .719" diameter



File No. E31557(M)

File No. LR20904

Mfr.'s Type 31099 Socket \$4.82

Lenses For Universal Lamp Housings

For T-2 Slide Base Lamps and T-2½ and T-3¼ Bayonet Base Lamps

Color	Flat Top Translucent	Each	Jeweled	Each	Domed Transparent	Each	Domed Translucent	Each	Domed Fluted	Each
Red	30200	.98	30100	1.46	30110	.49	30130	.51	30120	.49
Green	30212	1.03	30102	1.48	30112	.48	30132	.51	30122	.51
Blue	-	-	-	-	30113	.65	-	-	30124	.51
Amber	-	-	30106	1.74	30111	.65	-	-	30126	.51
Yellow	30214	.98	-	-	30114	.65	30131	.51	-	-
Clear	-	-	-	-	30116	.65	-	-	30125	.51
White	-	-	-	-	-	-	30133	.51	-	-

Cartridge Lamps, Lenses and Sockets

T-2 Indicator Cartridge Lamps, Sockets and Lenses

Lenses for Indicator & Pilot Sockets

Color	Translucent	Each	Translucent	Each
Amber	30140	2.23	-	-
Clear	30141	2.31	-	-
Red	30142	1.85	30147	1.85
Blue	30143	1.85	-	-
Green	30144	2.23	30149	1.51
Yellow	-	-	30145	1.92
White	-	-	30146	1.92

Indicator Sockets



Dimensions
Lenses: Diameter: .400"; Height: .425"
Socket: Front of panel to end of terminals: 1.0"
Mounting Hole: .372" diameter

Pilot Lamps

Lamp No.	Volts	Design Amps	Watts	Each
12PC	12.0	.170	2.0	2.12
24PC	24.0	.073	0.17	2.12
28PC	28.0	.040	1.1	1.94
120PC	120.0	.025	3.0	2.17

Pilot Sockets



Dimensions
Lenses: Diameter: .400"; Height: .425"
Socket: Front of panel to end of terminals: 1.20"
Mounting Hole: .372" diameter

Mfr.'s Type	Alternate No.	Base	Each
SM2A	30096	Solder Lugs	6.92

Indicator Lamps

Lamp No.	Volts	Design Amps	Watts	Each
918IC	12.0	.040	.48	2.34
926IC	16.0	.040	.64	2.29
933IC	24.0	.017	.42	2.29
934IC	24.0	.040	.96	2.29
938IC	28.0	.040	1.12	2.31
941IC	48.0	.040	1.92	2.31

