


HC-EVO-B24-SHWS-2SSM40-PLRBK

Order No.: 1407663

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1407663>

HEAVYCON EVO box mounting base, plastic, B24, with single locking latch, height: 84 mm, with gland, 2 x M40, one of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

Commercial data	
EAN	 4 046356 777261
Pack	1
Customs tariff	85389099
Gross weight in pieces	22.22 g
Country of Origin	PL

Product notesWEEE/RoHS-compliant since:
03/07/2012

Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data	
General data	
Note	For contact inserts HC-B24, BB46, D64, DD108, M
Design	B24
Height	84 mm
Width	57 mm

Length	144 mm
Housing type	Box mounting bases
Color	black
Locking type	With single locking latch
No. of cable exits	2
Cable exit	Lateral
Type of the screw connection	2x M40
Protective cover	No
Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Polyamide
Seal material	NBR
Material lock	Polyamide
Inflammability class according to UL 94	V0
Connection	One of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

Certificates

Certification

Certifications applied for:


Certification Ex:

Accessories

Item	Designation	Description
General		
1407705	HC-B24-SG-RBK	Replacement flat gasket for HEAVYCON EVO supporting base element type B24
1407701	HC-B24-SL-PLBK	Replacement single locking latch for HEAVYCON EVO housing type B24, PA
1407701	HC-B24-SL-PLBK	Replacement single locking latch for HEAVYCON EVO housing type B24, PA
1407709	HC-B24-SP-RBK	Profile gasket for HEAVYCON EVO supporting base element type B24
1407674	HC-K-KV-M40(16-28)BK	Plastic screw connection up to 5 bar, thread length: 10 mm, cable diameter: 16 - 28 mm, WAF 46, screw connection: M40

Drawings

Dimensioned drawing



Dimensional drawing

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;