



Connectix faceplates and back boxes have been designed to complement modules and quarter blanks.

Connectix faceplates are available in standard or compact sized single and dual versions, and have been designed to fit all industry standard modules. An Elite version with a modern sleek curved look is also available for high end specification applications.

All faceplates are supplied with fixing screws. They are finished as standard in an attractive high gloss white, but other colours are also available.

Connectix backboxes are available in single and dual gang with a choice of surface mounted and flush mounted dry lined wall versions.

Surface mount boxes feature knock outs for mini trunking adaptors.

Dry lining wall boxes are suitable for mounting into 6-14 mm thick board and can easily cope with irregular shaped aperture sizes. Swivelling snap out clamps will grip any standard thickness of building board tightly.

Features & Benefits

Faceplates

- ✘ Standard or compact size
- ✘ Single or dual faceplates
- ✘ Standard and Elite versions
- ✘ Industry standard size
- ✘ Euro or CCS fitting

Backboxes

- ✘ Tough shatter resistant material
- ✘ Designed for ease of use
- ✘ Uncluttered internal design

Ordering Information

Product Description	Part Number
Euro Faceplates	
Compact Single Gang Euro Faceplate	008-010-010-25
Compact Dual Gang Euro Faceplate	008-010-010-70
Standard Elite Single Gang Euro Faceplate	008-001-003-50
Standard Elite Dual Gang Euro Faceplate	008-001-003-60
Compact Elite Single Gang Euro Faceplate	008-001-003-70
Euro 1/4 Blank	008-001-004-65
Euro 1/2 Blank	008-001-004-70
CCS Faceplates	
Standard Single Gang CCS Faceplate	008-001-002-05
Standard Dual Gang CCS Faceplate	008-001-003-05
Compact Single Gang CCS Faceplate	008-001-002-06
Compact Dual Gang CCS Faceplate	008-001-003-06
Standard Elite Single Gang CCS Faceplate	008-001-002-01
Standard Elite Dual Gang CCS Faceplate	008-001-003-02
Compact Elite Single Gang CCS Faceplate	008-001-002-02
CCS 1/4 Blank	008-001-004-05
Back Boxes	
Dry Lining Single Gang	012-006-001-00
Dry Lining Double Gang	012-006-002-00
CCS 32mm White Single Gang	008-010-001-00

Specification

Dimensions	Faceplate			Back Box		
	Std	Dual	Compact	Std	Dual	Dry Line
						Std
Width (mm)	87	148	87	87	148	148
Height (mm)	87	87	87	87	87	87
External Depth (mm)	15	15	9	25	32	34
Internal Depth (mm)	-	-	-	23	30	34

Elite Faceplates

