
INSULATED PC SPACERS/SUPPORTS

· Board will be electrically insulated, eliminates need for insulating washers No tool required for installation
 Easy snap-in assembly


ADHESIVE LOCK-IN RELEASE SUPPORTS

- One end attaches to chassis with self adhesive pads
- · No drilling to chassis required leaving outside in perfect condition
- Other end snap into .062 (1.57) board

· Board is easily releasable for repair or upgrade



.125 (3.2)



CAT. NO.	L Length
9070	.187 (4.7)
9071	.250 (6.4)
9072	.375 (9.5)
9073	.500 (12.7)
9074	.625 (15.9)

Material: Nylon 6/6, UL Rated 94V-0

PC SPACER SUPPORTS

.250 (6.4)

.375 (9.5)

.500 (12.7)

.625 (15.9)

LENGTH

.187 (4.7)

.250 (6.4)

.375 (9.5)

.500 (12.7)

.625 (15.9)

.750 (19.1)

.875 (22.2)

9081

9082

9083

9084

CAT.

NO.

8822

8823

8824

8825

8826

8827


8828

- One end locks into chassis Other end supports the PC Board Ideal for mid supports of large boards
- Simplifies assembly for multiple support applications
 Reduces the amount of holes required in PC board

STURDY SUPPORT

.187 (4.8)

- . One end permanently attaches to .062 (1.57) chassis
- · Accommodates varying board thicknesses
- · Sturdy support due to large contact area



Material: Nylon 6/6, UL Rated 94V-0


Material: Nylon 6/6, UL Rated 94V-0



.100 (2.8)

SLIMLINE SUPPORT

- One end permanently attaches to .062 (1.57) chassis
- · Low protrusion under chassis
- · Small diameter frees up space on PC board



9057 9058 9059 9060

CAT.

NO.

9055

9056

LENGTH

.125 (3.2)

.187 (4.7)

.250 (6.4)

.375 (9.5)

.500 (12.7)

.625 (15.9)

Material: Nvlon 6/6, UL Rated 94V-0

REVERSE CHASSIS MOUNT SUPPORTS

Permanently attaches to .059 (1.51) - .065 (1.65) thick case from outside


• Provides flat clean cosmetic appearance • Ideal for low clearance applications or for mounting directly to case walls

.156 (4.0)

.213 (5.4)

LOCK-IN RELEASE

- End locks onto .062 (1.57) PC board
- · Board is positively locked until manually released
- · Board is easily releasable for repairs or upgrades




Material: Nylon 6/6, UL Rated 94V-0

.125 (3.2)

.187 (4.8)

SLIMLINE LOCK-IN

- End permanently attaches to .062 (1.57) PC board
- · Small footprint frees up PC board space



CAT. LENGTH NO. 9065 .250 (6.4) 9066 .375 (9.5) 9067 .500 (12.7) 9068 .625 (15.9)

Material: Nylon 6/6, UL Rated 94V-0

LENGTH

.250 (6.4)

.375 (9.5)

.500 (12.7)

.625 (15.9)

9061

9062

9063

9064