

Fusedrawer with and without Voltage Selector Insert

Standard or Medical Fuse drawer



Fuse drawer without voltage selector insert with shorting bar
(Fuse links not enclosed)

Fuse drawer with voltage selector insert
(Fuse links not enclosed)

**Description**

- Component
- Snap-in version from front side
- 2 Functions:
Fuseholder, Voltage Selectors
- Approved together with power entry module

Characteristics

- Fuse drawer meets requirements of medical standard IEC/EN 60601-1
The fuse drawer "Fingerflip" can be removed by hand
The fuseholder is accessible from the equipment front
- Designed for standard and medical applications
- Suitable for use in equipment according to IEC 60950

Other versions on request

- Fuse drawer with other voltage values

References

Fits to type:

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [CAD-Drawings](#), [Accessories](#), [Mounting instruction](#), [Detailed request for product](#)

Voltage Selector Inserts

Index	Marking on Voltage Selector Insert / Terminal No.			
	1	2	3	4
01	110	150	220	-
02	120	-	240	-
03	110	-	220	-
04	115	-	220	-
05	110	-	230	-
06	115	-	230	-
07	100	110	220	240
08	100	120	220	240
10	220	-	240	-
11	120	220	240	-
12	110	220	240	-
13	115	220	240	-
14	-	-	-	-
15	100	120	220	-
16	50 Hz	-	60 Hz	-
19	117	220	240	-
22	110	220	230	-
23	100	115	220	240
24	115	230	240	-
25	100	120	230	-
26	220	230	240	-
28	120	230	-	-
29	100	120	230	240
31	-	120	230	-
32	100	120	200	240

Index	Marking on Voltage Selector Insert / Terminal No.			
	1	2	3	4
33	110	120	220	240
34	100	115	230	240
36	100	110	120	-
37	100	110	230	240
38	110	127	230	-
40	110	220	240	120
41	100	115	230	-
42	200	230	240	-
44	1	2	3	4
45	100	220	230	240
47	100	-	120	-
48	100	110	230	-
49	110	220	230	240
51	100	-	-	-
52	120	220	230	240
53	001	-	-	-
54	021	022	032	042
55	230	-	115	-

Index "xx" matches the last two characters of the Order Number within the Variants

Variants

Mounting	Voltage Selectors	Fuseholder	Comment	Suitable for	Order Number
Extra-Safe		1-pole	-	1), 2), 3)	4301.1407
Extra-Safe		1-pole	spare fuse case	1), 2), 3)	4301.1411
Fingergrip		1-pole	-	1), 2), 3)	4301.1405
Fingergrip		1-pole	spare fuse case	1), 2), 3)	4301.1409
Extra-Safe		2-pole	-	1), 2), 3)	4301.1403
Extra-Safe		2-pole	shorting bar in the neutral side	1), 2), 3)	4301.1415
Fingergrip		2-pole	-	1), 2), 3)	4301.1401
Fingergrip		2-pole	shorting bar in the neutral side	1), 2), 3)	4301.1413
Extra-Safe	●	1-pole	-	1)	4301.1224.xx
Extra-Safe	●	1-pole	spare fuse case	1)	4301.2824.xx
Fingergrip	●	1-pole	-	1)	4301.1214.xx
Fingergrip	●	1-pole	spare fuse case	1)	4301.2814.xx
Extra-Safe	●	2-pole	-	1)	4301.1024.xx
Extra-Safe	●	2-pole	shorting bar in the neutral side	1)	4301.3537.xx
Fingergrip	●	2-pole	-	1)	4301.1014.xx
Fingergrip	●	2-pole	shorting bar in the neutral side	1)	4301.3536.xx

1) KEA, KFA;

2) KEA-Print (without voltage selector)

3) KM, DD11, DD12, DD21, DD22 (only 1-/2-pole, without voltage selector)

"xx" see Voltage Selector Insert Table

Packaging unit

50 Pcs