



# PRODUCT SPECIFICATION

<b>Brand</b>	C.K
<b>Product Range</b>	Ratchet crimping pliers & Coax Stripper
<b>Catalogue number</b>	As listed
<b>Date</b>	11/10/2012

<p><b>Range Description</b> Professional quality ratchet crimping pliers</p>		 <p style="text-align: center;">430026</p>		
<p><b>Features</b></p> <p><b>430026</b></p> <ul style="list-style-type: none"> <li>• High quality carbon steel - for durability</li> <li>• High compression pressure – for secure crimping</li> <li>• Deadlock system – for safe and precise crimping</li> <li>• Quick release lever – for ease of use</li> <li>• For Coax – BNC, TNC, 58, 59, 62, 8X, 140, 141, 174 (only 0.128" plugs), 210, 223, 303, 400</li> <li>• Display packed</li> </ul>				
<p><b>Range Description</b> Jokari Cable/Wire strippers</p>		 <p style="text-align: center;">300010</p>		
<p><b>Features</b></p> <p><b>30010</b></p> <ul style="list-style-type: none"> <li>• Razor sharp, preset stripping blades for fast, precise and damage free stripping of all common coaxial cables.</li> <li>• Also suitable for stripping 3-core flex.</li> <li>• Working Range 4,8 – 7,5 mm Ø</li> </ul>				
Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
430026	Ratchet crimping pliers for Coax	5051074300263	82032090	3
T30010	Jokari Coaxial Cable Stripper	4011391300101	82032090	18

Technical product information <b>430026</b>	
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship Damage caused through inappropriate use is not covered
Country of origin	Taiwan

Technical product information <b>T30010</b>	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	Jokari Tools are guaranteed for 2 years against imperfect materials or workmanship, except blades and knives Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Germany

## Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
430026	70	20	230	517	110	22	330	560
T30010	100	18	18	22	258	81	30	40

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
430026	127	355	78	1819		
T30010	215	320	125	920		

## Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
430026	16	Blister	27	Backing card			139	Box
T30010	8	Blister	9	Backing Card			202	Box