

Interactive Catalog Supplements Catalog PDFs

If you need detailed product information, or help choosing the right product for your application, see our **Interactive Catalog**. Use the **Interactive Catalog** to access the most complete and up-to-date information available.

The **Interactive Catalog** provides an extensive collection of product specifications, application data, and technical literature that can be searched based on criteria you select.

This PDF catalog information was published in November 2000.



Sensing and Control
**Interactive
Catalog...**

**Click this icon to try
the Interactive Catalog.**

Sensing and Control

Honeywell Inc.

11 West Spring Street

Freeport, IL 61032

Manual Switches

Toggle Switches



2-pole shown

FEATURES

- 2 or 3-position, momentary and maintained action
- 1 and 2-pole circuitry
- Rated up to 15 amps
- Lever-to-bushing seal
- Solder, screw, or quick-connect terminals
- UL recognized, CSA certified

Colored tab levers and special “on-on-on” circuitry can also be furnished.

TERMINAL CIRCUIT IDENTIFICATION


Terminal identifications in the order guides indicate which circuits are made in each position (i.e., 1-2 indicates circuit closure through terminals 1 and 2).

ELECTRICAL RATINGS


Rating Code	UL/CSA Rating
L192	10 Amps, 125, 250, 277 VAC ¼ HP, 125 VAC ½ HP, 250, 277 VAC 3 Amps, 125 VAC “L”
L191	15 Amps, 125, 250, 277 VAC ½ HP, 125 VAC 1 HP, 250, 277 VAC 5 Amps, 125 VAC (L)

MOUNTING DIMENSIONS

1-pole



2-pole



TS 2-POSITION ORDER GUIDE

No. Of Poles	Circuit(s) Made With Toggle At:		UL/CSA Rating Code	Screw Terminals	Solder Terminals	Quick-Connect Terminals
	Keyway Position	Opposite Keyway				
1	OFF	2-3 ON	L191	11TS15-2	11TS115-2	11TS95-2
	2-1 ON	2-3 ON	L191	11TS15-3	11TS115-3	11TS95-3
	OFF*	2-3 ON	L192	11TS15-4		11TS95-4
	2-1 ON*	OFF	L192	11TS15-6	11TS115-6	11TS95-6
	2-1 ON*	2-3 ON	L192	11TS15-8	11TS115-8	
2	OFF	2-3 & 5-6 ON	L191	12TS15-2	12TS115-2	12TS95-2
	2-1 & 5-4 ON	2-3 & 5-6 ON	L191	12TS15-3	12TS115-3	12TS95-3
	OFF*	2-3 & 5-6 ON	L192	12TS15-4		
	2-1 & 5-4 ON*	OFF	L192	12TS15-6		
	2-1 & 5-4 ON*	2-3 & 5-6 ON	L192	12TS15-8	12TS115-8	

TS 3-POSITION ORDER GUIDE

No. Of Poles	Circuit(s) Made With Toggle At:			UL/CSA Rating Code	Screw Terminals	Solder Terminals	Quick-Connect Terminals
	Keyway Position	Center Position	Opposite Keyway				
1	2-1 ON	OFF	2-3 ON	L191	11TS15-1	11TS115-1	11TS95-1
	2-1 ON*	OFF	2-3 ON	L192	11TS15-5	11TS115-5	11TS95-5
	2-1 ON*	OFF	2-3 ON*	L192	11TS15-7	11TS115-7	11TS95-7
2	2-1 & 5-4 ON	OFF	2-3 & 5-6 ON	L191	12TS15-1	12TS115-1	12TS95-1
	2-1 & 5-4 ON*	OFF	2-3 & 5-6 ON	L192	12TS15-5	12TS115-5	12TS95-5
	2-1 & 5-4 ON*	OFF	2-3 & 5-6 ON*	L192	12TS15-7		12TS95-7
	2-1 & 5-4 ON	2-1 & 5-6 ON	2-3 & 5-6 ON	L191	—		12TS95-10

* Marked toggle positions are momentary. All other positions are maintained.