

## Shrink sleeve - WMS 4,8 (15X9)R - 0800382

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Shrink sleeve, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, Perforated, Mounting type: Slide on, Cable diameter: 1.6-4.8 mm, Lettering field: 15 x 9 mm




The illustration shows WMS 6,4 (30X10)R

### Why buy this product

- The sleeves are pre-assembled for optimum use of material
- WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- The sleeves remain flexible after shrinking
- The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- Up to four markers per sleeve are separated by perforations

### Key commercial data

Packing unit	1 PCE
GTIN	 4 046356 626491
Weight per Piece (excluding packing)	296.8 GRM
Weight per piece (including packing)	312.4 GRM
Custom tariff number	39173200
Country of origin	China
Sales Key	B1 - Marking Assembly

### Technical data

#### Dimensions

Length (b)	15 mm
Width (a)	9 mm

#### Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-55 °C ... 135 °C

#### General

Color	white
Base element material	polyolefine

# Shrink sleeve - WMS 4,8 (15X9)R - 0800382

## Technical data

### General

Components	Halogen-free
Material	Polyolefine
Number of individual labels	1000
Number of individual labels per row	4

## Classifications

### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27400401
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC001530
ETIM 4.0	EC001530
ETIM 5.0	EC001530

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## Accessories

### Accessories

Ink ribbon - THERMOMARK-RIBBON 110-WMSU - 0801358



Ink ribbon, specifically for WMS... shrink sleeves, length: 300 m, width: 110 mm, color: black

## Shrink sleeve - WMS 4,8 (15X9)R - 0800382

### Accessories

Ink ribbon - THERMOMARK-RIBBON 64-WMSE BU - 5145737



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: blue

---

Ink ribbon - THERMOMARK-RIBBON 64-WMSE RD - 5145740



Ink ribbon, Length: 300000 mm, Width: 64 mm, Color: red

---

Media hub - THERMOMARK ROLL-ERH - 5146448



External media hub, for the THERMOMARK ROLL, for roll diameter of 150 to 400 mm

---

---