

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-52-0071](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 3.96mm Pitch KK® Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2478
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnection System
Packaging Alternative	08-52-0072 (Loose)
Product Name	KK®
UPC	800753758131

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.240/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Material Info

Old Part Number [2478-3-\(P909\)](#)

Reference - Drawing Numbers

Product Specification	PS-08-50
Sales Drawing	SD-2478




image - Reference only

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[2478Series](#)

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) , [5239](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030016
Terminator Die	0011402096
Hand Crimper	0638117500
Mini-Mac Applicator for KK® and Trifurcon™ Crimp Terminals	0638885000
FineAdjust™ Applicator with Special Cut-off	0639007300

Tab Width for IDT
Housing Terminals
Only

This document was generated on 08/21/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION