

D-Sub Backshells

DPPK Series




Features:

- Available in sizes 9, 15, 25 and 37
- Hinged single piece moulding with retaining latches
- Light weight and cost effective
- Compact and attractive design
- Long jackscrews with UNC 4-40 thread as standard, M2.5, M2.6 or M3 as option

Technical Specifications:

Material	: Nylon
Temp. Range	: -55°C to +105°C
Cable Strain Relief	: Cable clamp with self-tapping screws
Cable Diameter	: 3mm to 11mm
Locking Screws	: Long jackscrews with moulded top for colour coding
Cable Outlet	: Straight



Part Number	A	B
MC-DPPK9	32.4	31.3
MC-DPPK15	40.7	30.8
MC-DPPK25	54.4	37.3
MC-DPPK37	70.9	36

Dimensions : Millimetres

www.element14.com
www.farnell.com
www.newark.com



D-Sub Backshells

DPPK Series



Part Number Table

Description	Part Number
Backshell, Plastic, Vertical, Blk, 9Way	MC-DPPK9-K
Backshell, Plastic, Vertical, Blk, 15Way	MC-DPPK15-K
Backshell, Plastic, Vertical, Blk, 25Way	MC-DPPK25-K
Backshell, Plastic, Vertical, Blk, 37Way	MC-DPPK37-K
Backshell, Plastic, Black, 9Way, Pk50	MC-DPPK9-BULK/50
Backshell, Plastic, Black, 15Way, Pk50	MC-DPPK15-BULK/50
Backshell, Plastic, Black, 25Way, Pk50	MC-DPPK25-BULK/50
Backshell, Plastic, Black, 37Way, Pk50	MC-DPPK37-BULK/50
Backshell, Plastic, Vertical, Gry, 9Way	MC-DPPK9-GREY-K
Backshell, Plastic, Vertical, Gry, 15Way	MC-DPPK15-GREY-K
Backshell, Plastic, Vertical, Gry, 25Way	MC-DPPK25-GREY-K
Backshell, Plastic, Vertical, Gry, 37Way	MC-DPPK37-GREY-K
Backshell, Plastic, Vertical, Red, 9Way	MC-DPPK9-RED-K
Backshell, Plastic, Vertical, Red, 15Way	MC-DPPK15-RED-K
Backshell, Plastic, Vertical, Red, 25Way	MC-DPPK25-RED-K
Backshell, Plastic, Vertical, Red, 37Way	MC-DPPK37-RED-K
Backshell, Plastic, Vertical, Blue, 9Way	MC-DPPK9-BLUE-K
Backshell, Plastic, Vertical, Blu, 15Way	MC-DPPK15-BLUE-K
Backshell, Plastic, Vertical, Blu, 25Way	MC-DPPK25-BLUE-K
Backshell, Plastic, Vertical, Blu, 37Way	MC-DPPK37-BLUE-K
Backshell, Plastic, Vertical, Ylw, 9Way	MC-DPPK9-YELLOW-K
Backshell, Plastic, Vertical, Ylw, 15Way	MC-DPPK15-YELLOW-K
Backshell, Plastic, Vertical, Ylw, 25Way	MC-DPPK25-YELLOW-K
Backshell, Plastic, Vertical, Ylw, 37Way	MC-DPPK37-YELLOW-K
Backshell, Plastic, Vertical, Wht, 9Way	MC-DPPK9-WHITE-K
Backshell, Plastic, Vertical, Wht, 15Way	MC-DPPK15-WHITE-K
Backshell, Plastic, Vertical, Wht, 25Way	MC-DPPK25-WHITE-K
Backshell, Plastic, Vertical, Wht, 37Way	MC-DPPK37-WHITE-K

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
 www.farnell.com
 www.newark.com

