



**Tripp Lite**  
 1111 West 35th Street  
 Chicago, IL 60609 USA  
 Telephone: +(773) 869 1234  
 E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: RBC53

### UPS Replacement Battery Cartridge Kit for select Tripp Lite, Best, Powerware, Liebert and other UPS

#### Highlights

- Up to 30% longer runtime than basic replacements
- OEM certified premium batteries
- Rugged, leakproof construction
- Maintenance-free
- Wide operating temperature range



#### Description

Tripp Lite's premium UPS replacement battery cartridges breathe new life into UPS systems suffering from expired or weak internal batteries. Each replacement battery cartridge is carefully screened and certified to meet or exceed original manufacturer specifications and ships ready for installation into your UPS system. Reusable packaging holds expired batteries for recycling center delivery. Compatible with a wide variety UPS brands and models. See Tripp Lite's UPS replacement battery web page to confirm compatibility and quantity required.

#### Applications

- Extends the operating life of older UPS systems
- Restores or enhances runtimes of all UPS systems exhibiting reduced power failure runtime

#### Package Includes

- 3 12V UPS replacement batteries
- Instruction manual with installation, recycling and warranty information

#### Features

- Restore UPS runtime performance to its original runtime specifications
- Reusable packaging contains expired batteries for recycling center delivery
- Compatible with a variety of UPS brands

#### Specifications

<b>BATTERY</b>	
Included Battery Set	Includes 3 12V batteries
Typical battery lifespan	3 - 5 years, depending on host UPS operating conditions
<b>PHYSICAL</b>	
Shipping Dimensions (HWD/in)	6 x 7.5 x 12

<b>Shipping Dimensions (HWD/cm)</b>	15.2 x 19.1 x 30.5
<b>Shipping weight (lbs)</b>	19 (Package includes 3 batteries)
<b>Shipping weight (kg)</b>	8.6 (Package includes 3 batteries)
<b>Unit Dimensions (HWD/in)</b>	Each battery measures 3.6875 x 2.5 x 5.875
<b>Unit Dimensions (HWD/cm)</b>	Each battery measures 9.4 x 6.4 x 14.9
<b>ENVIRONMENTAL</b>	
<b>Relative Humidity</b>	0 - 95% non-condensing
<b>Operating Elevation (ft.)</b>	0 - 10,000
<b>Storage Elevation (ft.)</b>	0 - 50,000
<b>Operating Elevation (m)</b>	0-3000 m
<b>Storage Elevation (m)</b>	0 - 15,200 m
<b>WARRANTY</b>	
<b>Product Warranty Period (U.S. &amp; Canada)</b>	18-month limited warranty
<b>Product Warranty Period (International)</b>	1-year limited warranty
<b>Product Warranty Period (Mexico)</b>	1-year limited warranty
<b>Product Warranty Period (Puerto Rico)</b>	1-year limited warranty

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2544](http://www.tripplite.com/en/products/model.cfm?txtModelID=2544).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.