



Tripp Lite
 1111 West 35th Street
 Chicago, IL 60609 USA
 Telephone: +(773) 869 1234
 E-mail: saleshelp@tripplite.com

Model #: U042-036

36-ft. High-Speed USB2.0 A/B Active Device Cable (A Male to B Male)

Highlights

- 36-ft. (11m) USB A-B Active Cable
- Overcomes the 5-meter USB barrier
- Built-in repeater maintains high-speed USB 2.0 signal quality



Description

Tripp Lite's High-Speed USB 2.0 Active A-B cable overcomes the 5-meter USB distance limitation with an active repeater in the middle of the cable. Now USB printers and other devices can be located up to 36 ft. (11m) away from the computer in a single, non-daisy chainable run, with no need for extension cables. Full 480Mbps speed is maintained along the entire length of the cable. Backward compatible to USB 1.1. Plug-and-play, Windows and MAC compatible. The U042-036 provides up to 250mA of power to the connected device. If your device requires more than 250mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-036.

System Requirements

- A USB 2.0 port and USB 2.0 device (with type B jack) are required to meet USB 2.0 speeds. A USB 1.1 port and/or device can be used, but you will not be able to achieve USB 2.0 speeds.
- The U042-036 provides up to 250mA of power to the connected device. If your device requires more than 250mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-036.

Package Includes



- 36ft Hi-Speed USB 2.0 Active Cable

Features

- Connect a computer to a printer or other USB device up to 36 ft. away
- High-Speed USB 2.0 and USB 1.1 compatible
- Active repeater maintains 480Mbps signal integrity
- USB "A" to USB "B" connections
- Windows 98/ME/2000/XP/Vista/WIN7 and MAC compatible
- Cable length: 36 ft. (11m) Weight: 1 lb.
- Repeater Pod dimension: 16.75 x 57.3 x 31.7 (mm.) / 0.7 x 2.3 x 1.3 (in.)
- The U042-036 provides up to 250mA of power to the connected device. If your device requires more than 250mA of power, it will either need to have its own power supply; or, to be plugged into a powered USB 2.0 hub (such as [U222-007-R](#)) that is connected to the U042-036.

Specifications

OVERVIEW	
Intended Application	Connecting Peripherals

Cable Type	USB
INPUT	
Cable Length (ft.)	36
Cable Length (m)	10.97
UPC ASSIGNMENT	
Unit Carton UPC#	037332138712
PHYSICAL	
Color	Silver
Style	USB
CONNECTIONS	
Connector A	 USB A (MALE)
Connector B	 USB B (MALE)
Number of Connectors	2
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
U022-006	6-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
U022-015	15-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
U026-016	16-ft. USB2.0 A/A Active Extension Cable (USB-A M/F)	1
U026-10M	10-meter (33 ft.) USB2.0 A/A Hi-Speed Active Extension / Repeater Cable	1
U026-20M	20-meter (65 ft.) USB2.0 A/A Hi-Speed Active Extension / Repeater Cable	1
U042-025	25ft. High-Speed USB2.0 A/B Active Device Cable (A Male to B Male)	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=3643.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.