

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [74548-0111](#)  
**Status:** **Active**  
**Overview:** iPass™ Connector System  
**Description:** External iPass™ Mini Multi-Lane SAS Guide Frame for PCI/PCIe Add-In Cards, 1-by-1 Port Size, 1° Cage Angle, Port Keying 4

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**


Product Family	I/O Connectors
Series	<a href="#">74548</a>
Application	Module-to-Board
Comments	Port Keying 4
Component Type	Guide
Overview	<u>iPass™ Connector System</u>
Product Name	iPass™, Mini Multi-Lane, PCI Express*, SAS
Type	N/A
UPC	822350341813

**Physical**

Boot Color	N/A
Circuits (Loaded)	26
Circuits (maximum)	26
Durability (mating cycles max)	200
Gender	N/A
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	N/A
Net Weight	13.150/g
Number of Rows	2
Orientation	Horizontal
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm, 2.38mm, 3.20mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	0.5A
Grounding to Panel	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[74548Series](#)

**Mates With**

[74547 iPass™ Cable Assembly](#)

**Use With**

[75586 Receptacle](#)

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing

SD-74548-100

This document was generated on 09/05/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**