

General Information

Extended Product Type:	M35/26.FF
Product ID:	1SNA115140R2300
EAN:	3472591151404
Catalog Description:	M35/26.FF
Long Description:	M35/26.FF Power Terminal Blocks Feed-through

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Power Terminal Blocks

Ordering

EAN:	3472591151404
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	26.0 mm
Product Net Height:	66.0 mm
Product Net Depth:	44.0 mm
Product Net Weight:	0.064 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	120 mm
Package Level 1 Height:	57 mm
Package Level 1 Length:	130 mm
Package Level 1 Gross Weight:	0.64 kg
Package Level 1 EAN:	3472591151404
Package Level 2 Units:	300 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	300 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	19.7 kg
Package Level 3 Units:	7200 piece
Product Packing Type:	Box

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007-01-01
--------------	--

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity-Main Circuit UL/CSA:	Stud / Rigid 1x 10-2 AWG

Additional Information

Color:	Grey
Connecting Capacity-Main Circuit:	Stud / Flexible 1x 2.5-25 mm ² Stud / Rigid 1x 2.5-50 mm ²
Function:	Feed-through
IIT Publishing Status:	Level 0 - Information enabled
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Product Main Type:	M35/26.FF
Product Name:	Terminal block
Rated Cross-Section:	25 mm ²
Rated Current (I _n):	Main Circuit 101 A
Rated Short-time Withstand Current (I _{cw}):	for 1.0s 8000 A
Rated Voltage (U _r):	1000 V
Spacing:	26 mm

Certificates and Declarations (Document Number)

CSA Certificate:	TBD-from cat 2010
cUL Certificate:	1SND165000A0203
GOST Certificate:	1SND161005A1103

Classifications

Object Classification Code: X

