



The Choice Is Clear — Akro-Mils Has the Largest Selection of Clear Bins, Totes & Containers in the Industry!

 **AKRO-MILS®**

Clear AkroBins®

EXCLUSIVE
FROM AKRO-MILS
Clear Dust-Protection Lids


Organize inventory and keep parts in clear view with clear AkroBins. Heavy-duty bins securely stack atop each other, sit on shelving or hang from Akro-Mils louvered racks, panels, rails and carts.

- Molded of durable clear polypropylene, AkroBins are unaffected by weak acids and alkalis
- Sturdy, one-piece construction is water, rust and corrosion-proof
- Guaranteed not to crack or break under normal load conditions as stated in our 1-year limited warranty
- Crystal Clear lids available
- Length and width dividers sold separately
- Available in 14 sizes




30230SCLAR w/ 30231 Lid


Clear AkroBins	Outside Dim. Inches			
Model No.	L	W	H	Lid
30210SCLAR	5¾	4¾	3	30211CRY
30220SCLAR	7¾	4¾	3	30221CRY
30224SCLAR	10¾	4¾	4	30225CRY
30230SCLAR	10¾	5½	5	30231CRY
30234SCLAR	14¾	5½	5	-
30239SCLAR	10¾	8¼	7	-
30240SCLAR	14¾	8¼	7	-
30265SCLAR	18	8¼	9	-
30235SCLAR	10¾	11	5	30236CRY
30260SCLAR	18	11	10	-
30255SCLAR	10¾	16½	5	-
30250SCLAR	14¾	16½	7	-
30270SCLAR	18	16½	11	-
30320SCLAR	8¾	33	5	30321CRY



30653230SC



30618220SC



98636230SC



30016230SC

Clear AkroBin Louvered Floor Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided Floor Rack		
30651220SC	30220SCLAR	144
30651230SC	30230SCLAR	72
30651240SC	30240SCLAR	36
Double-Sided Floor Rack		
30653220SC	30220SCLAR	288
30653230SC	30230SCLAR	144
30653240SC	30240SCLAR	72

Clear AkroBin Louvered Panel Systems

Model No.	Bin Model No.	Bin Qty.
18" x 19" Wall Panel		
30618220SC	30220SCLAR	16
30618230SC	30230SCLAR	9
35" x 19" Wall Panel		
30636210SC	30210SCLAR	32
30636220SC	30220SCLAR	32
30636230SC	30230SCLAR	18
30636240SC	30240SCLAR	8
36" x 61" Wall Panel		
30161210SC	30210SCLAR	120
30161220SC	30220SCLAR	120
30161230SC	30230SCLAR	60
30161240SC	30240SCLAR	28

Clear AkroBin Louvered Bench Rack Systems

Model No.	Bin Model No.	Bin Qty.
27" x 8" x 19" Bench Rack		
98600210SC	30210SCLAR	30
98600220SC	30220SCLAR	30
98600230SC	30230SCLAR	12
36" x 8" x 20" Bench Rack		
98636210SC	30210SCLAR	40
98636220SC	30220SCLAR	40
98636230SC	30230SCLAR	18

Clear AkroBin Wire Shelving Systems

Model No.	Bin Model No.	Bin Qty.
AWS143630320SC	30320SCLAR	12
AWS143630240SC	30240SCLAR	36
AWS143630250SC	30250SCLAR	18
AWS184830260SC	30260SCLAR	24*
AWS183630265SC	30265SCLAR	18
AWS183630270SC	30270SCLAR	9*

*Bonus Bins are included at no extra charge.

Clear AkroBin Rail Hanging Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided Rail Rack		
30008220SC	30220SCLAR	96
30008230SC	30230SCLAR	48
30008240SC	30240SCLAR	24
Double-Sided Rail Rack		
30016220SC	30220SCLAR	192
30016230SC	30230SCLAR	96
30016240SC	30240SCLAR	48

Clear ShelfMax® Bins

Go deep! Clear 6-inch ShelfMax Bins expand storage capacity up to 85% over standard 4" bins.



- Exclusive! Rolled top edge for added strength when filled to capacity
- Durable clear polypropylene construction is far superior to corrugated bins
- Width dividers sold separately
- Available in 7 sizes



AWS143630040SC

Clear ShelfMax	Outside Dim. Inches		
Model No.	L	W	H
30040SCLAR	11%	4%	6
30048SCLAR	17%	4%	6
30080SCLAR	11%	8%	6
30088SCLAR	17%	8%	6
30090SCLAR	11%	6%	6
30094SCLAR	23%	6%	6
30098SCLAR	17%	6%	6

Clear ShelfMax Wire Shelving Systems

Model No.	Bin Model No.	Bin Qty.
AWS143630040SC	30040SCLAR	64
AWS143630080SC	30080SCLAR	32
AWS183630088SC	30088SCLAR	32
AWS143630090SC	30090SCLAR	40
AWS183630048SC	30048SCLAR	64
AWS183630098SC	30098SCLAR	40
AWS243630094SC	30094SCLAR	40

Clear ShelfMax Steel Shelving Systems

Model No.	Bin Model No.	Bin Qty.
AS1279040SC	30040SCLAR	80
AS1279080SC	30080SCLAR	40
AS1279090SC	30090SCLAR	50
AS1879048SC	30048SCLAR	80
AS1879088SC	30088SCLAR	40
AS1879098SC	30098SCLAR	50
AS2479094SC	30094SCLAR	50

Clear ShelfMax 12" Pick Rack Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided		
APRS040SC	30040SCLAR	64
APRS080SC	30080SCLAR	32
APRS090SC	30090SCLAR	40
APRSAST00SC	30040SCLAR 30090SCLAR	32/20
Double-Sided		
APRD040SC	30040SCLAR	128
APRD080SC	30080SCLAR	64
APRD090SC	30090SCLAR	80
APRDAST00SC	30040SCLAR 30090SCLAR	64/40

Clear ShelfMax 18" Pick Rack Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided		
APRS18048SC	30048SCLAR	64
APRS18088SC	30088SCLAR	32
APRS18098SC	30098SCLAR	40
APRS18AST00SC	30040SCLAR 30090SCLAR	32/20
Double-Sided		
APRD18048SC	30048SCLAR	128
APRD18088SC	30088SCLAR	64
APRD18098SC	30098SCLAR	80
APRD18AST00SC	30040SCLAR 30090SCLAR	64/40



AS1279090SC

Clear Shelf Bins

4-inch Shelf Bins are the industry standard for quality, durability and value. Clear shelf bins are molded from durable polypropylene to ensure identification of parts and supplies.

- Wide hopper front and molded-in label holder
- Built-in rear hanglock allows bin to tilt out for complete access
- Width dividers sold separately
- Available in 13 sizes



AWS143630130SC

AS1279130SC



30138SCLAR

30124SCLAR

30130SCLAR

30120SCLAR

Clear Shelf Bins Outside Dim. Inches

Model No.	L	W	H
30110SCLAR	11%	2%	4
30120SCLAR	11%	4%	4
30130SCLAR	11%	6%	4
30150SCLAR	11%	8%	4
30170SCLAR	11%	11%	4
30128SCLAR	17%	4%	4
30138SCLAR	17%	6%	4
30158SCLAR	17%	8%	4
30178SCLAR	17%	11%	4
30124SCLAR	23%	4%	4
30164SCLAR	23%	6%	4
30184SCLAR	23%	8%	4
30174SCLAR	23%	11%	4

Clear Shelf Bin Wire Shelving Systems

Model No.	Bin Model No.	Bin Qty.
AWS143630120SC	30120SCLAR	96
AWS143630130SC	30130SCLAR	60
AWS143630150SC	30150SCLAR	48
AWS143630170SC	30170SCLAR	36
AWS183630128SC	30128SCLAR	96
AWS183630138SC	30138SCLAR	60
AWS183630158SC	30158SCLAR	48
AWS183630178SC	30178SCLAR	36
AWS244830124SC	30124SCLAR	120
AWS244830164SC	30164SCLAR	66
AWS244830184SC	30184SCLAR	60*
AWS244830174SC	30174SCLAR	48*

*Bonus Bins are included at no extra charge.

Clear Shelf Bin Steel Shelving Systems

Model No.	Bin Model No.	Bin Qty.
12" Deep		
AS1279110SC	30110SCLAR	144
AS1279120SC	30120SCLAR	96
AS1279130SC	30130SCLAR	60
AS1279150SC	30150SCLAR	48
AS1279170SC	30170SCLAR	36
18" Deep		
AS1879128SC	30128SCLAR	96
AS1879138SC	30138SCLAR	60
AS1879158SC	30158SCLAR	48
AS1879178SC	30178SCLAR	36

Clear Shelf Bin 12" Pick Rack Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided		
APRS110SC	30110SCLAR	96
APRS120SC	30120SCLAR	64*
APRS130SC	30130SCLAR	40*
APRS150SC	30150SCLAR	32*
APRS170SC	30170SCLAR	24
Double-Sided		
APRD110SC	30110SCLAR	192
APRD120SC	30120SCLAR	128*
APRD130SC	30130SCLAR	80*
APRD150SC	30150SCLAR	64*
APRD170SC	30170SCLAR	48

*Bonus Bins are included at no extra charge.

Clear Shelf Bin 18" Pick Rack Systems

Model No.	Bin Model No.	Bin Qty.
Single-Sided		
APRS18128SC	30128SCLAR	72*
APRS18138SC	30138SCLAR	48*
APRS18158SC	30158SCLAR	36*
APRS18178SC	30178SCLAR	24
Double-Sided		
APRD18128SC	30128SCLAR	132*
APRD18138SC	30138SCLAR	84*
APRD18158SC	30158SCLAR	72*
APRD18178SC	30178SCLAR	48

*Bonus Bins are included at no extra charge.

Clear Super-Size AkroBins®

Akro-Mils Exclusive! 20", 24" and 30" Deep Clear Bins for Super-Size Storage. Large-capacity storage bins for organizing your heavy or bulky items.

- Heavy-duty bins molded in clear polypropylene, unaffected by weak acids or alkalis
- Sturdy, one-piece construction is water, rust and corrosion proof
- Extra large stacking containers feature anti-slide stop to prevent bins from shifting forward
- Reinforced side ribs add strength and prevent spreading when stacked or loaded
- Optional window inserts optimize interior space and keep contents visible
- Length and width dividers sold separately
- Available in 12 sizes



30293SCLAR

30" Deep!

AKRO-MILS EXCLUSIVE
FROM AKRO-MILS
Clear 20" & 30" Deep
Super-Size AkroBins



AWS24361288SC

AS3679293SC

Model No.	Outside Dim. Inches		
	L	W	H
30280SCLAR	20	12¾	6
30281SCLAR	20	12¾	8
30282SCLAR	20	12¾	12
30283SCLAR	20	18¾	12
30284SCLAR	23¾	8¼	7
30286SCLAR	23¾	11	7
30287SCLAR	23¾	11	10
30288SCLAR	23¾	16½	11
30289SCLAR	23¾	18¼	12
30290SCLAR	29¼	18¾	12
30292SCLAR	29¾	11	10
30293SCLAR	29¾	16½	11

Clear Super-Size AkroBin Wire Shelving Systems

Model No.	Bin Model No.	Bin Qty.	Shelves
AWS184830280SC	30280SCLAR	24	9
AWS184830281SC	30281SCLAR	18	7
AWS184830282SC	30282SCLAR	12	5
AWS184830283SC	30283SCLAR	8	5
AWS18485ABSC	30280SCLAR, 30281SCLAR, 30282SCLAR, 30283SCLAR	4 / 3 / 4 / 4*	6
AWS24360284SC	30284SCLAR	28	8
AWS24360287SC	30287SCLAR	16*	6
AWS24360288SC	30288SCLAR	12	3
AWS243605ABSC	30287SCLAR & 30288SCLAR	12/6*	3
AWS24361288SC	30288SCLAR	10	3

*Bonus Bins are included at no extra charge.

Clear Super-Size AkroBin Steel Shelving Systems

Model No.	Bin Model No.	Bin Qty.	Shelves
24" Deep			
AS2479284SC	30284SCLAR	32*	9
AS2479287SC	30287SCLAR	24*	3
AS2479288SC	30288SCLAR	12	4
AS2479ASSORTSC	30287SCLAR/30288SCLAR	12/6	3
36" Deep			
AS3679292SC	30292SCLAR	24	3
AS3679293SC	30293SCLAR	12	4
AS3679ASSORTSC	30292SCLAR/30293SCLAR	12/6	3

*Bonus Bins are included at no extra charge.

Clear Stak-N-Store Bins

Sturdy stacking storage bins for heavy and bulky items. Create tall, stable storage arrangements to save floor space. Extra-wide hopper front!

- Rolled top edge for added strength and durability
- Large comfort grip handles for easy lifting
- Available in 3 sizes



AWS183613014SC

AS187913018SC



13017SCLAR

13018SCLAR

13014SCLAR

Model No.	Outside Dim. Inches		
	L	W	H
13014SCLAR	17½	10¾	12½
13017SCLAR	15¼	19¾	12½
13018SCLAR	17½	16½	12½

Clear Stak-N-Store Wire Systems

Model No.	Bin Model No.	Bin Qty.	Shelves
AWS184813017SC	13017SCLAR	9	5
AWS183613014SC	13014SCLAR	12	5
AWS183613018SC	13018SCLAR	8	5

Clear Stak-N-Store Steel Shelving Systems

Model No.	Bin Model No.	Bin Qty.	Shelves
36" Deep			
AS187913014SC	13014SCLAR	16*	6
AS187913018SC	13018SCLAR	10	6
42" Deep			
AS187913017SC	13017SCLAR	12*	6


*Bonus Bins are included at no extra charge.

Crystal Clear AkroDrawers®

EXCLUSIVE
FROM AKRO-MILS
Crystal Clear AkroDrawers

Akro-Mils Exclusive! Crystal Clear AkroDrawers keep contents highly visible and allow for quick identification of parts and supplies. Made of a durable acrylic blend, clear AkroDrawers are ideal for a variety of environments from industrial to healthcare.

- Wide front handle for easy gripping
- Dividable to keep contents neatly separated and organized
- Sturdy backstop tab allows drawers to hang securely from shelves
- Width dividers sold separately
- Available in 9 sizes
- Two steel colors to choose from:



Textured Charcoal Gray

Textured Putty




3112CRY

31148CRY

31182CRY


31162CRY



AD3517P68CRY

Crystal Clear AkroDrawer Stackable Cabinets

Model No.	Drawer Model No.	Cabinet Color	Qty. of Drawers
35"W x 11"D x 22"H			
AD3511CAST2CRY AD3511PAST2CRY	31112CRY & 31162CRY	Textured Charcoal Gray Textured Putty	8 / 8
AD3511C62CRY AD3511P62CRY	31162CRY	Textured Charcoal Gray Textured Putty	24
AD3511C82CRY AD3511P82CRY	31182CRY	Textured Charcoal Gray Textured Putty	16
35"W x 17"D x 22"H			
AD3517CAST2CRY AD3517PAST2CRY	31118CRY & 31168CRY	Textured Charcoal Gray Textured Putty	8 / 8
AD3517C68CRY AD3517P68CRY	31168CRY	Textured Charcoal Gray Textured Putty	24
AD3517C88CRY AD3517P88CRY	31188CRY	Textured Charcoal Gray Textured Putty	16
AD3517CASTCRY AD3517PASTCRY	31168CRY & 31188CRY	Textured Charcoal Gray Textured Putty	12 / 8



ASC1879148CRY



APRD142CRY
w/ Mobile Kit

Crystal Clear AkroDrawers Outside Dim. Inches

Model No.	L	W	H
31142CRY	11%	3%	4%
31148CRY	17%	3%	4%
31162CRY	11%	5%	4%
31168CRY	17%	5%	4%
31164CRY	23%	5%	4%
31182CRY	11%	8%	4%
31188CRY	17%	8%	4%
31112CRY	11%	11%	4%
31118CRY	17%	11%	4%

Crystal Clear AkroDrawer Enclosed Shelving Systems

Model No.	Drawer Model No.	Qty. of Drawers
12" Deep		
ASC1279112CRY	31112CRY	36
ASC1279142CRY	31142CRY	108
ASC1279162CRY	31162CRY	72
ASC1279182CRY	31182CRY	48
ASC1279ASTCRY	31142CRY, 31162CRY, 31182CRY	30 / 36 / 12*
18" Deep		
ASC1879118CRY	31118CRY	36
ASC1879148CRY	31148CRY	108
ASC1879168CRY	31168CRY	72
ASC1879188CRY	31188CRY	48
ASC1879ASTCRY	31168CRY, 31188CRY	36 / 24

Crystal Clear AkroDrawer 12" Pick Rack Systems

Model No.	Bin Model No.	Qty. of Drawers
Single-Sided		
APRS112CRY	31112CRY	24
APRS142CRY	31142CRY	72
APRS162CRY	31162CRY	48
APRS182CRY	31182CRY	32
APRSASTCRY	31142CRY, 31162CRY, 31182CRY	18 / 24 / 8
Double-Sided		
APRD112CRY	31112CRY	48
APRD142CRY	31142CRY	144
APRD162CRY	31162CRY	96
APRD182CRY	31182CRY	64
APRDASTCRY	31142CRY, 31162CRY, 31182CRY	36 / 48 / 16

Crystal Clear AkroDrawer 18" Pick Rack Systems

Model No.	Bin Model No.	Qty. of Drawers
Single-Sided		
APRS18148CRY	31148CRY	72
APRS18168CRY	31168CRY	48
APRS18188CRY	31188CRY	32
APRS18118CRY	31118CRY	24
Double-Sided		
APRD18148CRY	31148CRY	144
APRD18168CRY	31168CRY	96
APRD18188CRY	31188CRY	64
APRD18118CRY	31118CRY	48

*Bonus Bins are included at no extra charge.

Tote Caddy

A simple, versatile, rugged tote with a large, comfortable handle

- Deep, oversized pockets hold many cleaning supplies or hardware and tools

Clear Tote Caddy Outside Dim. Inches

Model No.	L	W	H	Ctn. Qty.
09185SCLAR	13%	18%	9	6



09185SCLAR


Ultra-Clear InSight® Bins

Akro-Mils Exclusive! Ultra-Clear InSight Bins provide maximum visibility in a sleek, modern design. High-impact polycarbonate construction makes this unique bin the durable, modern storage solution for any setting.

- Bins stack with or without optional clear lids in place
- Rear hanging lip allows bins to securely hang from louvered panels and rails
- Autoclavable bin withstands temperatures up to 350° F
- Clear length and width dividers sold separately
- Available in 4 sizes



305A1



EXCLUSIVE FROM AKRO-MILS
Ultra-Clear Polycarbonate InSight Bins

Ultra-Clear InSight Outside Dim. Inches

Model No.	L	W	H	Lid
305A1	5¾"	4¼"	3¼"	305A2
305A3	7¾"	4¼"	3¼"	305A4
305A5	10"	4¼"	3¼"	305A6
305B1	10"	5½"	5¼"	305B2



30636BEIGEA3

Ultra-Clear InSight Louvered Panel Packages

Model No.	Description	Bin Qty.
30636BEIGEA1	35¾" x 19" Louvered Panel with 305A1	32
30636BEIGEA3	35¾" x 19" Louvered Panel with 305A3	32
30636BEIGEA5	35¾" x 19" Louvered Panel with 305A5	32
30636BEIGEB1	35¾" x 19" Louvered Panel with 305B1	18

Clear Akro-Grids

Versatile dividable storage containers for a variety of applications including: storage, work-in-process, automated material handling systems, kitting and distribution. Clear polypropylene grid boxes are a heavy-duty solution to separate and protect small parts during transport.

- Resists most solvents and chemicals
- Molded-in letter/number system for easy part tracking
- Length and width dividers sold separately
- Available in 9 sizes



33105SCLAR

33061



33168SCLAR



AWS183633168SC



33224SCLAR

Clear Akro-Grids Outside Dim. Inches

Model No.	L	W	H	Lid
33105SCLAR	10"	8¼"	5"	33011
33164SCLAR	16½"	10¾"	4"	33061
33166SCLAR	16½"	10¾"	6"	33061
33168SCLAR	16½"	10¾"	8"	33061
33220SCLAR	22"	17¾"	10"	33023
33223SCLAR	22½"	17¾"	3"	33023
33224SCLAR	22"	17¾"	4"	33023
33226SCLAR	22"	17¾"	6"	33023
33228SCLAR	22"	17¾"	8"	33023

Clear Akro-Grid Wire Shelving Systems

Model No.	Grid Model No.	Bin Qty.	Shelves
AWS183633166SC	33166SCLAR	24	9
AWS183633168SC	33168SCLAR	18	7
AWS2460M33224SC	33224SCLAR	36	12

MADE IN THE USA

AKRO-MILS®

1293 South Main Street, Akron, Ohio 44301 • Tel: 800.253.2467 • Fax: 330.761.6348 • sales@akro-mils.com
 In Canada: 8028 Torbram Road, Brampton, Ontario L6T 3T2 • Tel: 877.877.9680 • Fax: 905.791.4084 • sales@buckhorncanada.com
 Visit our website: akro-mils.com or 1-800-253-2467