



Soldering Tip - 1/4"

1/4" SERIES

COMPATIBLE STATIONS: Hexacon - 1/4" tip, American Beauty - 1/4" tip, Esico - 1/4" tip

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.



- **Fast heat recovering increases soldering speed**
- **Longer tip reduces manufacturing costs**
- **Fewer tip change overs**

Product Dimensions

42-628 Conical

Cross Reference: Esico 442-139, Esico 442-153, Hexacon HT513
0.8mm
10 units/case



42-355 Screwdriver

Cross Reference: American Beauty 716, Esico 422-108, Esico 422-132, Hexacon HT359
1.6
10 units/case



42-347 Screwdriver

Cross Reference: American Beauty 714, Esico 422-144, Esico 422-347, Hexacon HT358
2.4mm
10 units/case



42-117 Screwdriver, micro

Cross Reference: American Beauty 701, Esico 412-103, Esico 412-131, Hexacon HT451
3.2mm
10 units/case





Technical Data Sheet

44-390 Screwdriver

Cross Reference: American Beauty 721, Esico 420-106, Esico 420-119, Hexacon HT417
3.2mm
10 units/case

44-706 Screwdriver

Cross Reference: Esico 420-201, Hexacon HT586
3.2mm
10 units/case



44-715 Screwdriver, long

Cross Reference: Esico 420-114, Hexacon HT426
3.2mm
10 units/case



44-386 Screwdriver

4.0mm
10 units/case

43-754 Screwdriver

Cross Reference: Esico 413-102, Esico 413-134, Hexacon HT463, Hexacon HT397
4.8mm
10 units/case



44-352 Chisel


Cross Reference: American Beauty 715, Hexacon HT313, Hexacon HT202
4.8mm
10 units/case






44-611 Screwdriver, long

4.8
10 units/case




46-626 Screwdriver

Cross Reference: Esico 426-161, Esico 425-173, Hexacon HT552
4.8mm
10 units/case




46-912 Screwdriver

Cross Reference: Esico 426-189, Hexacon HT773
4.8mm
10 units/case



44-152 Screwdriver

Cross Reference: American Beauty 704, Esico 410-126, Esico 410-140, Hexacon HT553
6.4mm
10 units/case





Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW