




Isopropyl Alcohol (IPA) Wipes - 70%

1608-WIPES

99.8% pure anhydrous (containing the least water possible and no denaturant) isopropyl alcohol is excellent for tape head cleaning, defluxing, stencil cleaning, other light cleaning, and as a flux thinner. Avoid "bargain" alcohols for critical electronic cleaning. Cheap alcohols contain much more water, which slows drying and can cause oxidation, while "denatured" alcohols leave residues.



Pre-saturated wipes with 70% pure isopropyl alcohol

Convenient, lowlinting wipes are presaturated with 70% pure IPA.

- 70% IPA & 30% DI water
- Lint-free wipes
- Convenient packaging



Product Packaging

1608-100DSP
IPA Cleaning Wipes - Pop-up
Tub
100 ct
12 units/case



1608-100FL
IPA Cleaning Wipes - Flip-top
Tub
100 ct
12 units/case



1608-100R
IPA Cleaning Wipes - Refill
100 ct
6 units/case





Technical Information

Chemical & Physical Properties

Odor	Alcohol odor
Flash Point	53°F
VOC (EPA)	599 g/L
Density	0.86 at 25°C

Chemical Composition

CHEMICAL NAME	CAS #
2-Propanol	67-63-0

Performance & Application Data

1608-100DSP / -100FL / -100R fill	336 grams
1608-100DSP / -100FL / -100R wipe size	7-3/4" x 5-1/4"

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com

