



Absorb-Tip Foam Swab

2302

Precisely designed, manufactured and packaged to serve a wide variety of cleaning and maintenance needs. TechSwabs are manufactured in accordance with Techspray's rigid specifications, using specialized materials to ensure low particle generation. Cotton swabs are the most economical choice for high volume usage. Foam swabs are ideal for more precision cleaning where linting needs to be avoided.



Foam over cotton head for maximum absorbency

All foam swabs are manufactured with 100 pores per inch reticulated polyurethane foam, which ensures excellent absorbency while minimizing contamination. Tips are affixed by heat seal to prevent tip loss, even while saturated with solvent. Flexible tips provide versatility and softer touch, while rigid heads allow for more aggressive cleaning. 2302 swab has a foam head, with a cotton inner head for extra absorbency.

- Reticulated polyurethane foam
- Head thermally bonded
- High absorbency
- Low particulate count
- Cotton wrapped in foam for maximum absorbency
- Rigid head for firm touch

Product Packaging

2302-50
Absorb-Tip Foam Swab
50 ct
12 units/case

2302-1000
Absorb-Tip Foam Swab
1000 ct
1 units/case



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com



Technical Information

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
Email: tsales@techspray.com

Europe

ITW Contamination Control
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
Email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW



Techspray
P.O. Box 949, Amarillo, TX 79105
800-858-4043 • www.techspray.com