

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [19202-0049](#)
Status: **Active**
Overview: [Splices](#)
Description: NylaKrimp™ Butt Splice for 10-12 AWG Wire

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family [Splices](#)
 Series [19202](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 MolexKits Yes
 Overview [Splices](#)
 Product Name Butt, NylaKrimp™
 UPC 800753048218

Physical

Barrel Type Closed - Brazed
 Color - Resin Yellow
 Flammability 94V-2
 Insulation Nylon (PA)
 Material - Metal Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 2.703/g
 Packaging Type Bag
 Temperature Range - Operating -55°C to +105°C
 Wire Insulation Diameter 5.72mm max.
 Wire Size AWG 10, 12
 Wire Size mm² 3.30 - 5.00

Electrical

Voltage - Maximum 600V

Material Info

Old Part Number CS-N-346

Reference - Drawing Numbers

Product Specification PS-19902-011, PS-19902-013
 Sales Drawing 60002-11C, 6000211C



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

19202Series

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640015000
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	
Crimp Head for the	0640050300
AT-200™ Pneumatic	
Hand Tool	
Crimp Head for the	0640055000
AT-200™ Pneumatic	
Hand Tool	

This document was generated on 01/13/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION