

## MTA, CST-100 II, MT-6 and SL Connectors and Headers



### Product Highlights:

- SL-156 Product Line
- SL Series Series
- Wire-to-Board
- Applies To Wire/Cable
- Connector

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Line = SL-156
- Product Type = Connector
- Connector Type = Housing
- PCB Mount Retention = Without
- PCB Mount Alignment = Without
- Sealed = No
- CSA File Number = LR7189

#### Mechanical Attachment:

- Contact Retention = Without
- Mating Retention Type = Locking Ramp
- [Panel Mount Retention](#) = Without

#### Electrical Characteristics:

- Operating Voltage Reference = AC
- Operating Voltage (VAC) = 250

#### Body Features:

- Mating Retention = With
- Assembly Integration Feature = Without

#### Contact Features:

- Contact Type = Socket
- Contact Layout = In-Line
- Multiple Contact Types = Without

#### Housing Features:

- Connector Style = Receptacle
- Centerline (mm [in]) = 3.96 [0.156]
- Housing Style = Standard
- Housing Material = Nylon - GF
- Housing Color = Natural
- [Mating Alignment](#) = With

#### Configuration Features:

- [Number of Positions](#) = 2
- [Backwall/Post Interruption\(s\)](#) = Without
- Strain Relief = Without
- Number of Rows = 1

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant
- Agency/Standard = UL, CSA
- UL Rating = Listed
- CSA Rating = Certified
- UL File Number = E28476
- UL Flammability Rating = UL 94V-0

#### Environmental:

- Operating Temperature (°C [°F]) = -55 – +105 [-67 – +221]

#### Conditions for Usage:

- [Applies To](#) = Wire/Cable
- For Use With = SL .156 Contacts

#### Operation/Application:

- Application Use = Wire-to-Board

#### Packaging Features:

- Packaging Method = Bag
- Packaging Quantity = 500

#### Other:

<ul style="list-style-type: none"><li>• Mating Alignment Type = Polarization</li></ul>	<ul style="list-style-type: none"><li>• Series = SL Series</li><li>• Brand = AMP</li><li>• Comment = Unit Accepts 1.14[.045] Square or Round Post, Accepts Keying Plug 640254-1and 640255-1</li></ul>
--	---