

# BBP®85 Print Ribbons

www.BradyID.com

Benchmark Printers

## BBP®85 Printer Ribbons

- Choose from a variety of heavy-duty, smear-proof ribbons, including single color and multi-color paneled ribbons. These ribbons are uniquely designed with memory cells that communicate information to the BBP®85 printer.

### Single Color Print Ribbons

| Catalog # | Color   | Size Inch (mm) | Length Inch (mm) |
|-----------|---------|----------------|------------------|
| 13511     | Black   | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13510     | Black   | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13513     | White   | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13512     | White   | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13595     | Red     | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13514     | Red     | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13596     | Blue    | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13515     | Blue    | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13597     | Green   | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13516     | Green   | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13598     | Magenta | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13517     | Magenta | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13599     | Yellow  | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13518     | Yellow  | 8.800 (224.0)  | 200 ft. (60.9 m) |
| 13600     | Orange  | 6.250 (158.0)  | 200 ft. (60.9 m) |
| 13519     | Orange  | 8.800 (224.0)  | 200 ft. (60.9 m) |



Example Single Color Print Ribbon



Example Two Color Panel Print Ribbon



Example Four Color Panel Print Ribbon



Spare ribbon cassette (holder)  
Catalog # 13507

### Two Color Paneled Print Ribbons

| Catalog #                                                     | Color          | Ribbon Width Inch (mm) | Color Panel Length Inch (mm) | Overall Length   | Typical Yield From Ribbon  |
|---------------------------------------------------------------|----------------|------------------------|------------------------------|------------------|----------------------------|
| <b>8" Panels used to create 2 color signs up to 8" long</b>   |                |                        |                              |                  |                            |
| 13523                                                         | Black & Red    | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| 13522                                                         | Black & Red    | 8.800 (223.5)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| 13527                                                         | Black & Yellow | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| 13529                                                         | Black & Orange | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| 13704                                                         | Black & Green  | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| 13706                                                         | Black & Green  | 8.800 (223.5)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | One hundred 8" long labels |
| <b>15" Panels used to create 2 color signs up to 14" long</b> |                |                        |                              |                  |                            |
| 13521                                                         | Black & Red    | 6.250 (158.0)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13520                                                         | Black & Red    | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13525                                                         | Black & Blue   | 6.250 (158.0)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13524                                                         | Black & Blue   | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13526                                                         | Black & Yellow | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13528                                                         | Black & Orange | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13705                                                         | Black & Green  | 6.250 (158.0)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |
| 13707                                                         | Black & Green  | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Sixty 14" long labels      |

### Four Color Paneled Print Ribbons

| Catalog #                                                     | Color                 | Ribbon Width Inch (mm) | Color Panel Length Inch (mm) | Overall Length   | Typical Yield From Ribbon |
|---------------------------------------------------------------|-----------------------|------------------------|------------------------------|------------------|---------------------------|
| <b>8" Panels used to create 4 color signs up to 8" long</b>   |                       |                        |                              |                  |                           |
| 13533                                                         | Black/Red/Blue/Yellow | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | Fifty 8" long labels      |
| 13532                                                         | Black/Red/Blue/Yellow | 8.800 (223.5)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | Fifty 8" long labels      |
| 13537                                                         | Black/Red/Blue/Green  | 6.250 (158.0)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | Fifty 8" long labels      |
| 13536                                                         | Black/Red/Blue/Green  | 8.800 (223.5)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | Fifty 8" long labels      |
| 51448                                                         | Black/Red/Orange/Blue | 8.800 (223.5)          | 8.000 (203.2) Panels         | 200 ft. (60.9 m) | Fifty 8" long labels      |
| <b>15" Panels used to create 4 color signs up to 14" long</b> |                       |                        |                              |                  |                           |
| 13531                                                         | Black/Red/Blue/Yellow | 6.250 (158.0)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Thirty 14" long labels    |
| 13530                                                         | Black/Red/Blue/Yellow | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Thirty 14" long labels    |
| 13535                                                         | Black/Red/Blue/Green  | 6.250 (158.0)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Thirty 14" long labels    |
| 13534                                                         | Black/Red/Blue/Green  | 8.800 (223.5)          | 15.000 (381.0) Panels        | 200 ft. (60.9 m) | Thirty 14" long labels    |