

TELEVISION WALL MOUNTS

Television Wall Mounts

Applications:

New space-saving television/monitor mounts are ideal for today's home or office. As space-saving becomes more valuable in every room, GC mounts provide a modern alternative to bulky TV stands and home entertainment centers. By attaching your TV to a GC mount, you will save space while adding to the decor of your bedroom, den, office, bar or any room in the house. The high-tech, scratch resistant finish compliments today's contemporary lifestyles and television designs. In addition to saving space, GC wall mounts make watching TV easier. The 10° shelf tilt angle and the 90° left/right swivel lets you position the television for optimum viewing from any point in the room. GC wall mounts fit most 13", 19"/20" and 25"/27" televisions and monitors. All mounts include hardware for installation.



Fig. 1



Fig. 2



Fig. 3



Fig. 4



Fig. 5

Television Wall Mounts

Retail Part No.	Bulk Part No.	Figure Number	Description	Color
32-1810		1	Adjustable DVD/VCR Bracket. Tray 2.5-4.5"H x 12.5-17.5"W	Black
32-1810-WH		1	Adjustable DVD/VCR Bracket. Tray 2.5-4.5"H x 12.5-17.5"W	White
32-1815-CM		2	13" TV Ceiling Mount. Tray 14"W x 15.5"D. Holds 85 lbs.	Black
32-1815-WCM		2	13" TV Ceiling Mount. Tray 14"W x 15.5"D. Holds 85 lbs.	White
32-1816-WCM		2	19"/20" TV Ceiling Mount. Tray 20"W x 18"D. Holds 100 lbs.	White
32-1817-CM		2	25"/27" TV Ceiling Mount. Tray 25"W x 19.5"D. Holds 125 lbs.	Black
32-1817-WCM		2	25"/27" TV Ceiling Mount. Tray 25"W x 19.5"D. Holds 125 lbs.	White
32-1815		3	13" TV Mount. Tray 14"W x 15.5"D. Holds 85 lbs.	Black
32-1815-WH		3	13" TV Mount. Tray 14"W x 15.5"D. Holds 85 lbs.	White
32-1816		3	19"/20" TV Mount. Tray 20"W x 18"D. Holds 100 lbs.	Black
32-1816-WH		3	19"/20" TV Mount. Tray 20"W x 18"D. Holds 100 lbs.	White
32-1817		4	25"/27" TV Mount. Tray 25"W x 19.5"D. Holds 125 lbs.	White
32-1820 AK		5	Ceiling/Wall Anchor Kit with 4 bolts (for concrete)	Silver

Outdoor Antennas are Available Through a Partnership with Winegard.
Call Customer Service for Price and Availability.

Specifications:

Locks antenna or station signal for brighter, clearer TV and FM reception. Easily handles the largest residential outdoor TV antenna arrays. Automatic antenna control indicates position of antenna.

- Zinc Diecast, Weather Sealed Motor Housing
- Maximum Wind Load Area of 5 sq. ft.
- Brake Withstands 1,440 inch oz. of Torque
- 360° Rotation in One Minute
- Control 15 VAC, 60 Cycles, AC 0.7 amps
- Motor Operates on 24V AC
- 22 AWG 3 Conductor Lead Wire Required

Antenna Rotor

Retail Part No.	Bulk Part No.	Figure Number	Description
32-9015		6	Antenna Rotor
32-9015-CB		6	Controller Only



Fig. 6