

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84702-0006](#)
Status: **Active**
Overview: [RJ-45 Industrial Ethernet Plugs, Receptacles and Accessories](#)
Description: [EtherNet/IP, RJ-45, Punchdown Panel Mount Receptacle Jack](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Modular Jacks/Plugs
Series	84702
Component Type	Wire Jack
Magnetic	No
MolexKits	Yes
Overview	RJ-45 Industrial Ethernet Plugs, Receptacles and Accessories
Performance Category	5, 5e
Power over Ethernet (PoE)	N/A
Product Name	Industrial, RJ45
UPC	822348263059

Physical

Color - Resin	Black
Durability (mating cycles max)	500
Inverted / Top Latch	No
Jack Height	34.29mm
Keying to Mating Part	Yes
Lightpipes/LEDs	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon, Polyester
Net Weight	40.462/g
Orientation	Right Angle (Side Entry)
PCB Retention	None
Packaging Type	Bag
Panel Mount	With Flange
Pitch - Mating Interface	1.02mm
Ports	1
Positions / Loaded Contacts	8/8
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-40°C to +80°C
Termination Interface: Style	N/A
Wire/Cable Type	N/A

Electrical

Current - Maximum per Contact	1.5A
Grounding to Panel	N/A
Shielded	Yes
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-84702-004
---------------	--------------



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[84702Series](#)

Mates With

[84700-0002 Plug](#), [84702 Cable Assemblies](#)

Use With

[84700-0003 Dust Cover](#)

This document was generated on 02/21/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION