molex

Delivering streamlined behind-panel routings with MT, MPO/MTP* interfaces and IP67-sealed harsh-environmental protection with LC interfaces, Optical Electro Magnetic Interference (EMI) Shielding Adapters are ideal in networking and industrial applications

Optical Electro Magnetic Interference (EMI) shielding adapters are designed to address mechanical-design requirements limiting EMI and Radio Frequency Interference (RFI) emissions from front panels or enclosures. The adapters are constructed of either all diecast housings or as a half die-cast, half polymer housing.

Housings have an EMI gasket that seals the adapters to the panel. EMI adapters increase the shielding effectiveness while enhancing the front-panel aesthetics compared to traditional plastic adapters.


Features and Benefits

MPO to MT/ HMBT™ and IP67 Sealed LC to LC Adapters

or H	O (MTP*) front-interface to MT IBMT™ back-interface adapter es (106114 only)	Provide flexibility in fiber routing and reduce space requirements inside the box
LC i shu	7 sealed, ruggedized duplex nterface adapters with latching tters (106127-0100 and 27-0110 only)	Shutter latches to compress the seal and protect from moisture and dust ingress. Provides harsh- environment sealing
All El	MI Adapters	
Met	al die-cast housings	Provide Electro Magnetic Interference (EMI) protection
EMI	gaskets included	Provide Electro Magnetic Interference (EMI) seal between the adapter and mounting surface
Safe	ety shutters included	Provides dust protection, eye safety and reduces EMI when no connector is installed
Scre ava	ew- and snap-mount styles ilable	Provides mounting flexibility
desi	gle and multiple-port adapter ign (accepts one or four nectors)	Provides for design flexibility
alig	amic or phosphor bronze nment sleeves (where licable)	Accommodate singlemode (SM) and multimode (MM) performance

Optical EMI Shielding Adapters

106114	MPO/MTP* to MT or HMBT™ Adapters
106127	LC Duplex to LC Duplex Sealed Ruggedized Adapter
106114	MPO Adapter
106115	LC Duplex Adapters
106116	SC Adapter
106123	LC Quad Adapters



- A. MPO (MTP*) to HMBT[™] Quad Adapter B. MPO (MTP*) to HMBT[™] Simplex Adapter with Shutter
- C. LC Duplex Sealed Adapter with Latching Shutter
- D. MPO (MTP*) to MT Simplex Adapter with Shutter
- E. MPO (MTP*) to HMBT[™] Simplex Adapter with Shutter



MPO (MTP*) Adapters Series numbers 106115 LC Duplex Adapters 106116 SC Adapter 106123 LC Quad Adapters

molex

Specifications

Reference Information

Packaging: MTP tray, LC bag Mates With: MPO (MTP*), LC duplex connectors Use With: Optical Cable Assemblies and FlexPlane™ Optical Circuitry Designed In: Millimeters RoHS: Yes Halogen Free: Yes

Mechanical

Durability (min.): 200 mates and de-mates

Physical Housing: Metal (Zinc) for EMI versions Alignment Sleeve: Phosphor Bronze or Zirconia Ceramic Plating: Electro-less Nickel Operating Temperature: -40 to +85°C

Applications

Telecommunication Applications

- Data Centers
- Hubs
- Servers
- Routers
- Industrial Applications

– Test equipment

Aerospace/Defense Applications Storage

- ATM equipment
- Gigabit Ethernet testing equipment







High-End Servers

ATM Equipment

Optical EMI Shielding Adapters

molex

Ordering Information

Optical EMI Shielding Adapters

MPO (MTP*) to MT and HBMT[™] Adapters

Order No.	Cable Type	Mount Style	Shutter	Front Interface	Back Interface
106114-1150	- Simplex Quad	Screw	-	MPO (MTP*)	MT
106114-1160		Staggered Screw			
106114-1510		Screw	One Side		HBMT™ Clip
106114-1520		Snap			
106114-1530					
106127-0100	Duplex	Screw			LC Duplex Ruggedized, Ceramic Alignment Sleeve with IP67 Sealed Gasket
106127-0110			Latching	LC Duplex Ruggedized	LC Duplex Ruggedized, Phosphor Bronze Alignment Sleeve with IP67 Sealed Gasket

LC EMI Adapters

Order No.	Cable Type	Mount Style	Mount Angle	Shutter	Mount From
106115-3100		Screw	45°	One Side	
106115-4100		Snap		One side	
106115-1100	Duplex		Ctoricht	None	Front
106115-1110		Screw		One Side	
106115-1120				Two Sides	
106115-2100			Straight	None	
106115-2110		Snap		One Side	
106115-2120				Two Sides	
106115-3200		Single Screw	45°		Rear
106123-0500	Quad	Snap		One Side	Redi
106123-0600		Screw	Straight		E
106123-0700		SCIEW			Front

MPO EMI Adapters

Order No.	Cable Type	Mount Style	Mount Angle	Shutter	Mount From
106114-1100	Simplex	Screw	Straight	One Side	Front
106114-1200		Snap			
106114-3000		Screw	- 45°		
106114-4000		Snap			
106114-0100		SingleScrew			Deer
106114-3200	Quad	Screw		None	Rear

SC EMI Adapters

Order No.	Cable Type	Mount Style	Mount Angle	Shutter	Mount From
106116-2000		Snap	Straight		Front
106116-2100	Simplex	Screw		One Side	FIOIL
106116-4500		Single Screw	45°		Rear
106116-1000	SC Duplex EMI Adapter	Snap/Screw	Straight	Snap-On	Front

www.molex.com/product/emiadapters.html