

# Kellems® Wire Management Products

## PolyTuff® Non-Metallic Liquidtight Fittings



UL Listed to Type  
4X, 12 and 13

### Straight with Male Non-Metallic Liquidtight Fittings

| Trade Size (metric designator) | Black Catalog Number | Gray Catalog Number |
|--------------------------------|----------------------|---------------------|
| 1/4 (6)                        | F2025                | —                   |
| 3/8 (9)                        | P038NBKA             | P038NGYA            |
| 1/2 (13)                       | P050NBKA             | P050NGYA            |
| 3/4 (19)                       | P075NBKA             | P075NGYA            |
| 1 (25)                         | P100NBKA             | P100NGYA            |
| 1 1/4 (32)                     | P125NBK              | P125NGY             |
| 1 1/2 (38)                     | P150NBK              | P150NGY             |
| 2 (51)                         | P200NBK              | P200NGY             |

Note: Fittings are to be used with PolyTuff I and PolyTuff II.  
See page T-113 for additional technical data and dimensional drawings.  
3/8" Liquidtight conduit fitting have 1/2 N.P.T. male threads.



P075NGYA



P125NGY

### SwivelLok® Multi-Position with Male Non-Metallic Liquidtight Fittings

| Trade Size (metric designator) | Black Catalog Number | Gray Catalog Number |
|--------------------------------|----------------------|---------------------|
| 3/8 (9)                        | PS0389NBK            | PS0389NGY           |
| 1/2 (13)                       | PS0509NBK            | PS0509NGY           |
| 3/4 (19)                       | PS0759NBK            | PS0759NGY           |
| 1 (25)                         | PS1009NBK            | PS1009NGY           |

Note: Fittings are to be used with PolyTuff I and PolyTuff II.  
See page T-113 for additional technical data and dimensional drawings.  
3/8" Liquidtight conduit fitting have 1/2 N.P.T. male threads.



PS0509NGY - SwivelLok®

### Fixed 90° Fittings for Non-Metallic Conduit

| Trade Size (metric designator) | Black Catalog Number | Gray Catalog Number |
|--------------------------------|----------------------|---------------------|
| 1/4 (6)                        | F20259               | —                   |
| 3/8 (9)                        | P0389NBK             | P0389NGY            |
| 1/2 (13)                       | P0509NBK             | P0509NGY            |
| 3/4 (19)                       | P0759NBK             | P0759NGY            |
| 1 (25)                         | P1009NBK             | P1009NGY            |
| 1 1/4 (32)                     | P1259NBK             | P1259NGY            |

Note: Fittings are to be used with PolyTuff I and PolyTuff II.  
See page T-113 for additional technical data and dimensional drawings.  
3/8" Liquidtight conduit fitting have 1/2 N.P.T. male threads.



P1259NGY

### SwivelLok® Flexible Conduit Kit

| Trade Size (metric designator) | Fitting and Conduit   | Catalog Number |
|--------------------------------|-----------------------|----------------|
| 1/2 (13)                       | 2 PS0509NGY, 6' G1050 | PS05GYKIT      |
| 3/4 (19)                       | 2 PS0759NGY, 6' G1075 | PS07GYKIT      |

Note: See page T-113 for additional technical data and dimensional drawings.



PS05GYKIT