

SAFETY DATA SHEET
C4 HEAVY DUTY FLOOR CLEANER**1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING**

PRODUCT NAME C4 HEAVY DUTY FLOOR CLEANER

PRODUCT NO. SVTN5NGCB

SUPPLIER James Briggs Ltd.
Salmon Fields
Royton, Oldham, Lancashire,
England OL2 6HZ
0161 627 0101
0161 627 0971
sds@jamesbriggs.co.uk

2 HAZARDS IDENTIFICATION

Irritating to eyes and skin.

CLASSIFICATION Xi;R36/38.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
DISODIUM METASILICATE	229-912-9	6834-92-0	1-5%	C;R34 Xi;R37
PHOSPHATE ESTER		72283-31-9	1-5%	Xi;R36/38.
SODIUM HYDROXIDE	215-185-5	1310-73-2	< 1%	C;R35
TRIDECYL ALCOHOL ETHOXYLATE		9043-30-5	1-5%	Xn;R22. Xi;R41.

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES**INHALATION**

Move the exposed person to fresh air at once. Rinse nose and mouth with water. Get medical attention if any discomfort continues.

INGESTION

Remove victim immediately from source of exposure. Rinse mouth thoroughly. Drink plenty of water. Get medical attention.

SKIN CONTACT

Remove affected person from source of contamination. Remove contaminated clothing. Wash the skin immediately with soap and water.

Get medical attention if irritation persists after washing.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids.

Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES**EXTINGUISHING MEDIA**

This product is not flammable. Use fire-extinguishing media appropriate for surrounding materials.

6 ACCIDENTAL RELEASE MEASURES**SPILL CLEAN UP METHODS**

Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Do not contaminate water sources or sewer. Flush with plenty of water to clean spillage area.

7 HANDLING AND STORAGE**USAGE PRECAUTIONS**

Avoid spilling, skin and eye contact.

STORAGE PRECAUTIONS

Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

C4 HEAVY DUTY FLOOR CLEANER

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
SODIUM HYDROXIDE	WEL				2 mg/m3	

WEL = Workplace Exposure Limit.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits

PROTECTIVE EQUIPMENT**ENGINEERING MEASURES**

No particular ventilation requirements.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit. Use chemical cartridge protection with appropriate cartridge.

HAND PROTECTION

Use protective gloves.

EYE PROTECTION

Use approved safety goggles or face shield.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of skin contact.

HYGIENE MEASURES

DO NOT SMOKE IN WORK AREA! Wash at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes wet or contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Liquid
COLOUR	Pink
ODOUR	Characteristic
SOLUBILITY	Soluble in water
RELATIVE DENSITY	>1.0 @20°C

10 STABILITY AND REACTIVITY**STABILITY**

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid contact with acids.

HAZARDOUS DECOMPOSITION PRODUCTS

No specific hazardous decomposition products noted.

11 TOXICOLOGICAL INFORMATION**INHALATION**

May cause irritation to the respiratory system.

INGESTION

May cause burns in mucous membranes, throat, oesophagus and stomach. May cause stomach pain or vomiting.

SKIN CONTACT

Irritating to skin. Prolonged or repeated exposure may cause severe irritation. Acts as a defatting agent on skin. May cause cracking of skin, and eczema. May cause allergic contact eczema. May cause sensitisation by skin contact.

EYE CONTACT

May cause severe irritation to eyes. Risk of serious damage to eyes. Surfactant or detergent eye injury due to liquid splashes or dust.

C4 HEAVY DUTY FLOOR CLEANER

ROUTE OF ENTRY

Ingestion. Skin and/or eye contact.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

DEGRADABILITY

The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

GENERAL

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

No transport warning sign required.

ADR CLASS

Not classified for transportation.

MARINE POLLUTANT

No.

15 REGULATORY INFORMATION

LABELLING



Irritant

RISK PHRASES

R36/38

Irritating to eyes and skin.

SAFETY PHRASES

S2

Keep out of the reach of children

S24/25

Avoid contact with skin and eyes.

S26

In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S46

If swallowed, seek medical advice immediately and show this container or label.

DETERGENT LABELLING

< 5%

Anionic surfactants

Non-ionic surfactants

EDTA and salts thereof

Perfumes

Contains

BENZYL BENZOATE,d-LIMONENE,LINALOL SYNTHETIC

UK REGULATORY REFERENCES

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002.

The Control of Substances Hazardous to Health Regulations 2002.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961.

Control of Pollution (Special Waste Regulations) Act 1980.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Preparations Directive 1999/45/EC.

STATUTORY INSTRUMENTS

Chemicals (Hazard Information and Packaging) Regulations.

C4 HEAVY DUTY FLOOR CLEANER

Control of Substances Hazardous to Health.

APPROVED CODE OF PRACTICE

Classification and Labelling of Substances and Preparations Dangerous for Supply.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

Introduction to Local Exhaust Ventilation HS(G)37.

CHIP for everyone HSG(108).

16 OTHER INFORMATION

REVISION DATE 05/08/2010

REV. NO./REPL. SDS GENERATED 14

RISK PHRASES IN FULL

- | | |
|--------|-----------------------------------|
| R22 | Harmful if swallowed. |
| R34 | Causes burns. |
| R35 | Causes severe burns. |
| R36/38 | Irritating to eyes and skin. |
| R37 | Irritating to respiratory system. |
| R41 | Risk of serious damage to eyes. |

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.