

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [02-08-1201](#)
Status: **Active**
Overview: [Disk Drive Power Connector](#)
Description: [Disk Drive Power Connection System, Female Crimp Terminal, Reel, Phosphor Bronze, AWG 14-20](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-8981-4M*/4P* \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	8980
Application	Power
Crimp Quality Equipment	Yes
Overview	Disk Drive Power Connector
Product Name	Disk Drive Power
UPC	800753615939

Physical

Durability (mating cycles max)	50
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.223/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.03-2.74mm
Wire Size AWG	14, 16, 18, 20
Wire Size mm ²	N/A

Material Info

Old Part Number	8980-3C
-----------------	---------

Reference - Drawing Numbers

Product Specification	PS-8981-4M*/4P*
Sales Drawing	SD-8980-3*




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

8980Series

Use With

15-24-4048

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030037
Terminator Die	0011402282
Hand Crimp Tool	0638117000
Mini-Mac™	0638929000

Applicator for
 Disk Drive Power
 Connector System,
 Female 14-20 AWG

Japan

Description	Product #
-------------	-----------

Applicator for M21 1A 0571023000
Bench Press, 14-22
AWG Wire

This document was generated on 04/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION