

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [16-02-0105](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: SL™ Crimp Terminal, Series 70021, Male, with Tin (Sn) Plated Contact, 24-30 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-70021 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	70021
Application	Signal
Crimp Quality Equipment	Yes
Overview	C-Grid® Products
Packaging Alternative	16-02-0108 (Loose)
Product Name	SL™
UPC	800753595651

Physical


Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.094/g
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size AWG	24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number 70021-0004

Reference - Drawing Numbers

Product Specification [PS-70021](#)
 Sales Drawing [SD-70021-0*04_0*21](#), [SD-70021-0004](#)



EU RoHS

ELV and RoHS Compliant

REACH SVHC

Contains SVHC: No Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70021Series](#)

Use With

[70066 Housing](#), [70107 Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool For SL™ Crimp Terminals	0638258800
Insertion Tool	0011020022
Extraction Tool	0011030036
FineAdjust™	0639003400
Applicator for Male Crimp Terminal, 24-30 AWG Wire	
FineAdjust™	0639014500
Applicator for Crimp	

Terminal, Male, 28	
AWG, 41 Strands/44	
AWG Wire	
T2 Terminator	<u>0639103400</u>
Tooling Die	
Japan	
Description	Product #
Applicator for M211A	<u>0570173000</u>
Bench Press, 22-30	
AWG Wire	
Hand Insertion Tool	<u>0570336000</u>

This document was generated on 02/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION