

Lockout Stations

www.BradyID.com/lockouttagout

LOCKOUT STATION



Shown without optional lockable clear acrylic door

Extra-Large Lockout Station

- Ideal for locking out both mechanical and electrical control points
- Constructed of sturdy polystyrene with pre-drilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back and sides (includes 8 hooks)
- Built-in lock rail holds 20-25 locks
- Dimensions: 30"H x 25"W x 5-1/4"D
- Available with or without lockable door
- Components:
 - 10 - All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 - Large Univ. Valve Lockout w/Blocking Arm (50899 and 65403)
 - 2 - 120V Snap-On Breaker Lockouts (65387)
 - 2 - 120/277V Clamp-On Breaker Lockouts (65396)
 - 2 - 480/600V Clamp-On Breaker Lockouts (65397)
 - 2 - Universal Multi-Pole Breaker Lockouts (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 2 - Cleats for 120/277V Clamp-On Lockouts (65404)
 - 2 - Cleats for 480/600V Clamp-On Lockouts (65406)
 - 1 - Wall Switch Lockout (65392)
 - 1 - 110V Electrical Plug Lockout (65674)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 - 1/4" to 1" Ball Valve Lockout (65666)
 - 1 - 1-1/4" to 3" Ball Valve Lockout (65669)
 - 2 - 1" to 2-1/2" Gate Valve Lockouts (65560)
 - 1 - 1" to 6-1/2" Adjustable Gate Valve Lockout (64057)
 - 2 - Labeled Lockout Hasps (65960)
 - 18 - Keyed different safety padlocks (99552) or steel padlocks (99500)
 - 25 - Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties
 - 1 Station with "Lockout Station" legend

Catalog # Description

Open Style Without Doors

99693	Station w/ Components and 18 Safety Padlocks, 25 Tags
99694	Station w/ Components and 18 Steel Padlocks, 25 Tags
50993	Extra-Large Lockout Station (empty)
Enclosed Style With Lockable Doors	
99696	Station w/ Components and 18 Safety Padlocks, 25 Tags
99700	Station w/ Components and 18 Steel Padlocks, 25 Tags
50995	Extra-Large Enclosed Lockout Station (empty)

LOCKOUT STATION



Shown with optional lockable clear acrylic door

Large Lockout Station

- Provides everything you need for locking out all types of valves and plugs
- Constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Pegboard-style holes for hooks drilled into back (includes 6 hooks)
- Built-in lock rail holds 15-20 locks
- Dimensions: 26"H x 19-1/2"W x 5"D
- Available with or without lockable door
- Components:
 - 1 - All Purpose Cable Lockout w/ 8' Sheathed Cable (50943)
 - 1 - Large Univ. Valve Lockout w/Blocking Arm (50899 and 65403)
 - 1 - 110V Electrical Plug Lockout (65674)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 - 1/4" to 1" Ball Valve Lockout (65666)
 - 1 - 1" to 2-1/2" Gate Valve Lockout (65560)
 - 1 - 1" to 6-1/2" Adj. Gate Valve Lockout (64057)
 - 2 - Labeled Lockout Hasps (65960)
 - 12 - Keyed different safety padlocks (99552) or steel padlocks (99500)
 - 25 - Heavy duty, re-usable lockout tags w/ nylon cable ties. Tag legend options:
 - Danger Do Not Operate (65520)
 - Precaucion No Hacer Funcionar (121518)
 - Peligro No Operar (98219)
 - 1 Station with "Lockout Station" or "Estacion de Bloqueo" legend

Catalog # Description

Open Style Without Doors

99699	English Station w/ Components and 12 Safety Padlocks, 25 "Danger Do Not Operate" Tags
121508	Spanish Station w/ Components and 12 Safety Padlocks, 25 "Precaucion No Hacer Funcionar" Tags
121512	Spanish Station w/ Components and 12 Safety Padlocks, 25 "Peligro No Operar" Tags
99697	English Station w/ Components and 12 Steel Padlocks, 25 "Danger Do Not Operate" Tags
50994	English Open Style Station (empty)
121509	Spanish Open Style Station (empty)
Enclosed Style With Lockable Doors	
99703	English Enclosed Station w/ Components and 12 Safety Padlocks, 25 "Danger Do Not Operate" Tags
99704	English Enclosed Station w/ Components and 12 Steel Padlocks, 25 "Danger Do Not Operate" Tags
50996	English Enclosed Station (empty)

LOCKOUT STATION



Small Lockout Station

- Ideal for locking out all types of electrical control points
- Constructed of sturdy white polystyrene with predrilled holes for easy wall mounting
- Built-in lock rail holds 10-15 locks
- Pegboard-style holes for hooks drilled into back (includes 4 hooks)
- Dimensions: 18"H x 12"W x 4"D
- Components:
 - 1 - Mini Cable Lockout (50940)
 - 2 - 120V Snap-On Breaker Lockouts (65387)
 - 2 - 120/277V Clamp-On Breaker Lockouts w/ cleats (65396)
 - 2 - 480/600V Clamp-On Breaker Lockouts w/ cleats (65397)
 - 2 - Universal Multi-Pole Breaker Lockouts (66321)
 - 1 - Oversized Breaker Lockout (65329)
 - 1 - Wall Switch Lockout (65392)
 - 1 - 110V Electrical Plug Lockout (65674)
 - 1 - 3-in-1 Electrical Plug Lockout (PLO23)
 - 1 - Small fuse blockout (65690)
 - 1 - Large fuse blockout (65691)
 - 2 - Labeled Lockout Hasps (65960)
 - 6 - Keyed different safety padlocks (99552) or steel padlocks (99500)
 - 12 - Heavy duty, re-usable lockout tags (65520) w/ nylon cable ties
 - 1 Station with "Lockout Station" legend

Catalog # Description

99706	Station w/ Components & 6 Safety Padlocks, 12 Tags
99707	Station w/ Components & 6 Steel Padlocks, 12 Tags
50997	Small Lockout Station (empty)